



# GreenPerform Highbay G5

## BY698P G5 LED200/CW PSU NB GM L3m

GreenPerform Highbay G5, 121 W, 20500 lm, 6500 K, 55°

The GreenPerform Highbay G5 continues the GreenPerform family’s enviable reputation for reliable performance. Not only does it deliver leading system efficacy and extended long-term quality, it also promises Unified Glare Rating (UGR) control with compact dimensions. GreenPerform Highbay G5 is also fully compatible with IoT software such as Interact, which is a scalable, future-proof control system. The family also has a series that supports cold room applications with 100% humidity and no condensation. All benefits that make this robust, optimized, and versatile family suitable for almost all industrial applications.

### Product data

| General Information                |             | Operating and Electrical    |                   |
|------------------------------------|-------------|-----------------------------|-------------------|
| Number of gear units               | 1 unit      | Beam angle of light source  | 115 degree(s)     |
| Gear                               | -           | Light source color          | 865 cool daylight |
| Driver included                    | Yes         | Optic type                  | Narrow beam       |
| Light source engine type           | LED         | Luminaire light beam spread | 55°               |
| Value ladder                       | Performance | Unified glare rating CEN    | 22                |
| Warranty period                    | 5 years     | Effective projected area    | 0 m²              |
| Light Technical                    |             | Input Voltage               | 220 to 240 V      |
| Luminous Flux                      | 20,500 lm   | Line Frequency              | 50 or 60 Hz       |
| Correlated Color Temperature (Nom) | 6500 K      | Inrush current              | 41.6 A            |
| Luminous Efficacy (rated) (Nom)    | 169 lm/W    | Inrush time                 | 0.665 ms          |
| Color rendering index (CRI)        | 80          | Power Consumption           | 121 W             |
| Number of light sources            | 1           | Power Factor (Fraction)     | 0.95              |

## GreenPerform Highbay G5

|  |                          |
|--|--------------------------|
| Connection                                 | Flying leads/wires       |
| Cable                                      | Cable 3.0 m without plug |
| Number of products on MCB of 16 A type B 6 |                          |
| Suitable for random switching              | Yes                      |
| Protection class IEC                       | Safety class I           |

### Controls and Dimming

|                   |                |
|-------------------|----------------|
| Dimmable          | -              |
| Control interface | -              |
| Maximum dim level | Not applicable |

### Mechanical and Housing

|                              |  |
|------------------------------|--|
| Housing Material             | Aluminum die-cast                            |
| Reflector material           | -  |
| Optic material               | Polycarbonate                                |
| Optical cover material       | Polycarbonate                                |
| Housing Color                | Grey   |
| Mounting device              | Suspension set simple, standard              |
| Optical cover finish         | Clear  |
| Overall height               | 99 mm  |
| Overall diameter             | 330 mm                                       |
| Ingress protection code      | IP65 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK08 [5 J vandal-protected]                  |
| Optical cover type           | Clear dome                                   |
| Net Weight (Piece)           | 2.940 kg                                     |

### Approval and Application

|                   |   |
|-------------------|---|
| Glow-wire test    | Temperature 650 °C, duration 30 s           |
| Flammability mark | For mounting on normally flammable surfaces |

|                                    |  |
|------------------------------------|--|
| CE mark                            | Yes  |
| ENEC mark                          | -  |
| Photobiological risk               | Photobiological risk group 1 @200mm to EN62778 |
| Photobiological risk specification | 0.2 m  |
| EU RoHS compliant                  | Yes  |
| Performance ambient temperature Tq | 35 °C  |
| Ambient temperature range          | -30 °C to 50 °C                                |

### UV

|                                 |                     |
|---------------------------------|---------------------|
| UV-C radiation                  | 0 W                 |
| UV-C irradiance defined at 0.2m | 0 mW/m <sup>2</sup> |


### Initial Performance (IEC Compliant)

|                             |                       |
|-----------------------------|-----------------------|
| Luminous flux tolerance     | -10% / +10%           |
| Initial chromaticity        | (0.317, 0.338) SDCM<5 |
| Power consumption tolerance | +/-10%                |

### Product Data

|                                 |                                   |
|---------------------------------|-----------------------------------|
| Order product name              | BY698P G5 LED200/CW PSU NB GM L3m |
| Full product name               | BY698P G5 LED200/CW PSU NB GM L3m |
| Full product code               | 872110330794100                   |
| Order code                      | 911401539845                      |
| Material Nr. (12NC)             | 911401539845                      |
| Numerator - Quantity Per Pack   | 1                                 |
| EAN/UPC - Product/Case          | 8721103307941                     |
| Numerator - Packs per outer box | 1                                 |
| EAN/UPC - Case                  | 8721103307941                     |

## Dimensional drawing



## GreenPerform Highbay G5

