



FastSet

SM150C LED35S/840 PSU L1160

FastSet, 28 W, 3500 lm, 4000 K, Frosted, IP40 | Wire-protected

Philips FastSet SM150C is a batten family mainly for school lighting application where surface mounted or suspended applications are required. It provides 600mm/1200mm/1500mm length options with IP40 protection (front side). It offers max 130lm/w system efficacy which helps better energy saving for schools as well.

Product data

General Information		Controls and Dimming	
Light source engine type	LED	Dimmable	No
Light Technical		Control interface	-
Luminous Flux	3,500 lm	Mechanical and Housing	
Correlated Color Temperature (Nom)	4000 K	Housing Material	Metal-Plastic
Luminous Efficacy (rated) (Nom)	125 lm/W	Optical cover material	Polycarbonate
Color rendering index (CRI)	>80	Housing Color	White RAL 9003
Light source color	840 neutral white	Optical cover finish	Frosted
Effective projected area	0.17 m²	Overall length	1,160 mm
Operating and Electrical		Overall width	160 mm
Input Voltage	220-240 V	Overall height	64 mm
Line Frequency	50 or 60 Hz	Dimensions (Height x Width x Depth)	64 x 160 x 1160 mm
Inrush current	14.2 A	Ingress protection code	IP40 [Wire-protected]
Power Consumption	28 W	Mech. impact protection code	IK03 [0.35 J reinforced]
Power Factor (Fraction)	0.9	Optical cover type	Polycarbonate bowl/cover foggy
Number of products on MCB of 16 A type B	36	Net Weight (Piece)	1.790 kg
Protection class IEC	Safety class I	Approval and Application	
		Flammability mark	For mounting on normally flammable surfaces

CE mark	Yes
Ambient temperature range	0 to +35 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<=3
Power consumption tolerance	+/-10%
Product Data	
Order product name	SM150C LED35S/840 PSU L1160

Full product name	SM150C LED35S/840 PSU L1160
Full product code	871951492968599
Order code	92968599
Material Nr. (12NC)	911401543191
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514929685
Numerator - Packs per outer box	4
EAN/UPC - Case	8719514929777

Dimensional drawing

