



# FastSet

## SM150C LED50S/840 PSU L1440

FastSet, 40 W, 5000 lm, 4000 K, Frosted, IP40 | Wire-protected

Philips FastSet SM150C is a batten family mainly for school lighting application where surface mounted or suspended applications are required. It provides 600mm/1200mm/1500mm length options with IP40 protection (front side). It offers max 130lm/w system efficacy which helps better energy saving for schools as well.

### Product data

General Information		Controls and Dimming	
Light source engine type	LED	Dimmable	No
		Control interface	-
Light Technical		Mechanical and Housing	
Luminous Flux	5,000 lm	Housing Material	Metal-Plastic
Correlated Color Temperature (Nom)	4000 K	Optical cover material	Polycarbonate
Luminous Efficacy (rated) (Nom)	125 lm/W	Housing Color	White RAL 9003
Color rendering index (CRI)	>80	Optical cover finish	Frosted
Light source color	840 neutral white	Overall length	1,440 mm
Effective projected area	0.21 m <sup>2</sup>	Overall width	160 mm
		Overall height	64 mm
Operating and Electrical		Dimensions (Height x Width x Depth)	64 x 160 x 1440 mm
Input Voltage	220-240 V	Ingress protection code	IP40 [Wire-protected]
Line Frequency	50 or 60 Hz	Mech. impact protection code	IK03 [0.35 J reinforced]
Inrush current	14.2 A	Optical cover type	Polycarbonate bowl/cover foggy
Power Consumption	40 W	Net Weight (Piece)	2.290 kg
Power Factor (Fraction)	0.9		
Number of products on MCB of 16 A type B	36	Approval and Application	
Protection class IEC	Safety class I	Flammability mark	For mounting on normally flammable surfaces

CE mark	Yes
Ambient temperature range	0 to +35 °C
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<=3
Power consumption tolerance	+/-10%
<b>Product Data</b>	
Order product name	SM150C LED50S/840 PSU L1440

Full product name	SM150C LED50S/840 PSU L1440
Full product code	871951492971599
Order code	911401543491
Material Nr. (12NC)	911401543491
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514929715
Numerator - Packs per outer box	4
EAN/UPC - Case	8719514929807

## Dimensional drawing

