



# Greenspace Flex

## RS378B P11 940 PSD-E WW S

Greenspace Flex, 11 W, 940 neutral white, DALI, IP20 | Finger-protected

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

### Product data

General Information	
Light source engine type	LED
Value ladder	Performance
Light Technical	
Luminous Flux	2,150 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	90 lm/W
Color rendering index (CRI)	>90
Light source color	940 neutral white
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Power Consumption	11 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	-
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	DALI
Control interface	DALI
Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Polymethyl methacrylate
Housing Color	Grey
Optical cover finish	Opal
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]
Optical cover type	PMMA
Net Weight (Piece)	0.300 kg

Approval and Application	
CE mark	Yes
Ambient temperature range	-20 to +45 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%

## Greenspace Flex

Power consumption tolerance	+/-10%
-----------------------------	--------

### Product Data

Order product name	RS378B P11 940 PSD-E WW S
Full product name	RS378B P11 940 PSD-E WW S
Full product code	911401546571

Order code	911401546571
------------	--------------

Material Nr. (12NC)	911401546571
---------------------	--------------

Numerator - Quantity Per Pack	1
-------------------------------	---

Numerator - Packs per outer box	24
---------------------------------	----

## Dimensional drawing

