



# Truefashion Projector GCGM

## ST700T LED20 930PC PSU MB 1C WH

Truefashion Projector GCGM, 21 W, 930 warm white, 24°, IP20 | Finger-protected

Truefashion Projector is offering a retail segment with attractive outlook design, excellent quality of light & dedicated light recipe as well as system connectivity, to create a comfortable ambiance and impressive shopping experience to stimulate the store sales for retail customers.

### Warnings and Safety

- 3 years

### Product data

General Information		Beam angle of light source	
Light source replaceable	No	Beam angle of light source	120 degree(s)
Number of gear units	1 unit	Light source color	930 warm white
Driver included	Yes	Optic type	Beam angle 24°
Light source engine type	-	Luminaire light beam spread	24°
Service tag	Yes	Unified glare rating CEN	16
Value ladder	Specification	<b>Operating and Electrical</b>	
Warranty period	3 years	Input Voltage	220 to 240 V
<b>Light Technical</b>		Line Frequency	50 or 60 Hz
Luminous Flux	1,605 lm	Power Consumption	21 W
Correlated Color Temperature (Nom)	3000 K	Power Factor (Fraction)	0.9
Luminous Efficacy (rated) (Nom)	76 lm/W	Connection	Track
Color rendering index (CRI)	>90	Cable	-
		Number of products on MCB of 16 A type B	-

# Truefashion Projector GCGM

Suitable for random switching	No
Protection class IEC	Safety class II

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Maximum dim level	Not applicable

## Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Fixation material	Aluminum
Housing Color	White
Optical cover finish	Clear
Overall length	164 mm
Overall height	185 mm
Overall diameter	66 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	-
Optical cover type	Lens
Net Weight (Piece)	0.450 kg

## Approval and Application

CE mark	Yes
---------	-----

ENEC mark	-
EU RoHS compliant	Yes
Ambient temperature range	-20 to +35 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.422, 0.386) SDCM<3
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.14 %
Median useful life L70B50	50,000 hour(s)
Median useful life L80B50	50,000 hour(s)
Median useful life L90B50	32,600 hour(s)

## Product Data

Order product name	ST700T LED20 930PC PSU MB 1C WH
Full product name	ST700T LED20 930PC PSU MB 1C WH
Full product code	911401546761
Order code	911401546761
Material Nr. (12NC)	911401546761
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Dimensional drawing



