



GreenUp Magnetic Flex

ST307M ST P9 940 PSU-E MB

GreenUp Magnetic Flex, 9 W, 675 lm, 4000 K

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Magnetic Flex is a comprehensive product family with magnetic design which supports an easier and flexible way of installation and commissioning. It offers a complete range of options with product diversity and control availability. GreenUp Magnetic Flex gives you a plenty of flexibility to create the lighting magics.

Product data

General Information		Power Consumption	
Light source engine type	-	Power Consumption	9 W
Value ladder	Value	Power Factor (Fraction)	0.9
		Number of products on MCB of 16 A type B	-
		Protection class IEC	Safety class III
Light Technical		Controls and Dimming	
Luminous Flux	675 lm	Dimmable	No
Correlated Color Temperature (Nom)	4000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	75 lm/W		
Color rendering index (CRI)	>90	Mechanical and Housing	
Light source color	940 neutral white	Housing Material	Aluminium
Unified glare rating CEN	19	Optical cover material	Polycarbonate
		Housing Color	Black
		Optical cover finish	Clear
Operating and Electrical		Ingress protection code	IP20 [Finger-protected]
Input Voltage	48 V	Mech. impact protection code	IK03 [0.3 J]
Line Frequency	- Hz		
Inrush current	0.15 A		

GreenUp Magnetic Flex

Optical cover type	Polycarbonate micro lens optic
Net Weight (Piece)	0.194 kg

Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	ST307M ST P9 940 PSU-E MB
--------------------	---------------------------

Full product name	ST307M ST P9 940 PSU-E MB
Full product code	872016951797499
Order code	911401548332
Material Nr. (12NC)	911401548332
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169517974
Numerator - Packs per outer box	20
EAN/UPC - Case	8720169518582

Dimensional drawing

