



GreenUp Magnetic Flex

ST307M TG P15 940 PSU-E MB

GreenUp Magnetic Flex, 15 W, 940 neutral white, IP20 | Finger-protected

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Magnetic Flex is a comprehensive product family with magnetic design which supports an easier and flexible way of installation and commissioning. It offers a complete range of options with product diversity and control availability. GreenUp Magnetic Flex gives you a plenty of flexibility to create the lighting magics.

Product data

General Information	
Light source engine type	-
Value ladder	Value
Light Technical	
Luminous Flux	1,275 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	85 lm/W
Color rendering index (CRI)	>90
Light source color	940 neutral white
Unified glare rating CEN	19
Operating and Electrical	
Input Voltage	48 V
Line Frequency	- Hz
Inrush current	0.15 A
Power Consumption	15 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	-
Protection class IEC	Safety class III
Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing Material	Aluminium
Optical cover material	Polycarbonate
Housing Color	Black
Optical cover finish	Clear

GreenUp Magnetic Flex

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Polycarbonate bowl/cover
Net Weight (Piece)	0.323 kg

Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	ST307M TG P15 940 PSU-E MB
Full product name	ST307M TG P15 940 PSU-E MB
Full product code	872016951799899
Order code	911401548632
Material Nr. (12NC)	911401548632
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169517998
Numerator - Packs per outer box	12
EAN/UPC - Case	8720169518605

Dimensional drawing

