



PowerBalance G4

RC650B LED40S840 PSU W60L60 TWN

PowerBalance G4, 138.7 lm/W, 840 neutral white

PowerBalance G4 (RC650 range) is a complete office lighting family which creates a modern, flexible, and comfortable environment that fosters creativity and innovation. It provides multiple control options (Interact office, Interact pro, POE) to make your office energy efficient and easy to manage.

Product data

General Information		Operating and Electrical	
Number of gear units	1 unit	Input Voltage	100 to 277 V
Driver included	Yes	Line Frequency	50 or 60 Hz
Light source engine type	LED	Initial CLO power consumption	N.A. W
Service tag	Yes	Average CLO power consumption	N.A. W
Value ladder	Specification	Inrush current	5.56 A
Warranty period	3 years	Inrush time	20 ms
Light Technical		Power Consumption	35 W
Luminous Flux	4,855 lm	Power Factor (Fraction)	0.9
Correlated Color Temperature (Nom)	4000 K	Connection	Screw connection block 3-pole
Luminous Efficacy (rated) (Nom)	138.7 lm/W	Cable	-
Color rendering index (CRI)	>80	Number of products on MCB of 16 A type B	33
Beam angle of light source	120 degree(s)	Suitable for random switching	No
Light source color	840 neutral white	Protection class IEC	Safety class I
Optic type	Reflector	Controls and Dimming	
Luminaire light beam spread	100° x 100°	Dimmable	No
Unified glare rating CEN	16	Driver/power unit/transformer	Power supply unit (On/Off)
		Control interface	-
		Constant light output	No

PowerBalance G4

Maximum dim level	Not applicable
Mechanical and Housing	
Housing Material	Steel
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Textured
Overall length	603 mm
Overall width	603 mm
Overall height	70 mm
Dimensions (Height x Width x Depth)	70 x 603 x 603 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Polycarbonate
Net Weight (Piece)	5.300 kg
Approval and Application	
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes

ENEC mark	-
EU RoHS compliant	Yes
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
Median useful life L80B50	50,000 hour(s)
Median useful life L90B50	37,045 hour(s)

Product Data

Order product name	RC650B LED40S840 PSU W60L60 TWN
Full product name	RC650B LED40S840 PSU W60L60 TWN
Full product code	911401549761
Order code	911401549761
Material Nr. (12NC)	911401549761
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Dimensional drawing

