



# GreenPerform ultra efficient panel RC199B

## RC199X LED38/840 WIA W30L120 CAU UE

GreenPerform ultra efficient panel RC199B, 170 lm/W, 840 neutral white, InterAct Pro

GreenPerform ultra efficient panel is a direct lit panel with up to 170lm/w system efficacy (PSU driver) in the market. It offers 3 typical dimensions: 600x600; 300x1200 and 600x1200mm to fit most of indoor applications. Interact system option and Dali interface are available for wide option for system connection. Its lower UGR offers better visual comfort as well.

### Product data

General Information		Operating and Electrical	
Number of gear units	1 unit	Number of light sources	24
Gear	-	Light source color	840 neutral white
Driver included	Yes	Optic type	Beam angle 100°
Light source engine type	LED	Unified glare rating CEN	22
Value ladder	Specification		
Warranty period	3 years		
Light Technical			
Luminous Flux	3,800 lm	Input Voltage	200 to 240 V
Correlated Color Temperature (Nom)	4000 K	Line Frequency	50 to 60 Hz
Luminous Efficacy (rated) (Nom)	170 lm/W	Inrush current	4.9 A
Color rendering index (CRI)	80	Inrush time	56 ms
		Power Consumption	22 W
		Power Factor (Fraction)	0.9
		Connection	-

# GreenPerform ultra efficient panel RC199B


<b>Number of products on MCB of 16 A type B 40</b>	
Suitable for random switching	Not applicable
Protection class IEC	Safety class II
<b>Controls and Dimming</b>	
Dimmable	Wireless Dim
Control interface	InterAct Pro
Maximum dim level	0% (digital)
<b>Mechanical and Housing</b>	
Housing Material	Aluminum extruded
Optic material	Polystyrene
Optical cover material	Polystyrene
Housing Color	White RAL 9003
Mounting device	-
Optical cover finish	Diamond
Overall length	1,195 mm
Overall width	295 mm
Overall height	34 mm
Overall diameter	1,195 mm
Dimensions (Height x Width x Depth)	34 x 295 x 1195 mm
Ingress protection code	IP20/40 [Finger-protected, Emitting surface]
Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	PS
Net Weight (Piece)	1.500 kg

<b>Approval and Application</b>	
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +45 °C

<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

<b>Product Data</b>	
Order product name	RC199X LED38/840 WIA W30L120 CAU UE
Full product name	RC199X LED38/840 WIA W30L120 CAU UE
Order code	911401549944
Material Nr. (12NC)	911401549944
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4

## Dimensional drawing



## GreenPerform ultra efficient panel RC199B

