



# GreenPerform Batten G3 BN398C

## BN398X LED69/840 L1200 L1 W OP

GreenPerform Batten G3 BN398C, 49 W, 6800 lm, 4000 K, Opal, Wireless

GreenPerform batten BN398C is a cost competitive linear solution with good performance and multiple lumen output for retail and industry applications. It offers surface mount and suspension installations to cater for different mounting options. Its multiple optic designs accommodate different applications as well.

### Product data

General Information		Luminaire light beam spread	
Number of gear units	1 unit		-
Gear	-	Effective projected area	0 m <sup>2</sup>
Driver included	Yes	<b>Operating and Electrical</b>	
Light source engine type	LED	Input Voltage	220-240 V
Value ladder	Performance	Line Frequency	50 or 60 Hz
Warranty period	3 years	Inrush current	19 A
<b>Light Technical</b>		Inrush time	420 ms
Luminous Flux	6,800 lm	Power Consumption	49 W
Correlated Color Temperature (Nom)	4000 K	Power Factor (Fraction)	0.95
Luminous Efficacy (rated) (Nom)	138.77551020408163 lm/W	Connection	-
Color rendering index (CRI)	≥80	Cable	Cable 0.3 m without plug
Number of light sources	4	Number of products on MCB of 16 A type B	13
Beam angle of light source	- degree(s)	Suitable for random switching	Not applicable
Light source color	840 neutral white	Protection class IEC	Safety class I
Optic type	Opal		

# GreenPerform Batten G3 BN398C

## Controls and Dimming

Dimmable	Wireless Dim
Control interface	Wireless
Maximum dim level	20%

## Mechanical and Housing

Housing Material	Metal
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Housing Color	White
Mounting device	Mounting bracket
Optical cover finish	Opal
Overall length	1,188 mm
Overall width	58 mm
Overall height	58 mm
Dimensions (Height x Width x Depth)	58 x 58 x 1188 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Without lens
Net Weight (Piece)	1.690 kg

## Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 1 @200mm to EN62778

Photobiological risk specification	0.2 m
EU RoHS compliant	No
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 °C to 40 °C

## UV

UV-C radiation	0 W
UV-C irradiance defined at 0.2m	0 mW/m <sup>2</sup>


## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<23
Power consumption tolerance	+/-10%

## Product Data

Order product name	BN398X LED69/840 L1200 L1 W OP
Full product name	BN398X LED69/840 L1200 L1 W OP
Full product code	692382865759800
Order code	911401550602
Material Nr. (12NC)	911401550602
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828657598
Numerator - Packs per outer box	1
EAN/UPC - Case	6923828657598

## Dimensional drawing



## GreenPerform Batten G3 BN398C

