



CoreLine Downlight gen5

DN142B 10S/830 PSU-E UGR19

CoreLine Downlight gen5, 9.8 W, D150 mm, 1200 lm, 3000 K, UGR19, Facetted reflector, IP20

Philips CoreLine Downlight delivers on the CoreLine promise of innovative, easy to use and high-quality recessed downlights. The CoreLine Downlight range is suitable for one-to-one conventional luminaire replacements, with an attractive TCO that helps your customers make the switch to LED. These recessed indoor downlights offer uniform light distribution for use in general lighting and office applications (UGR 19). They also deliver instant energy savings and have a much longer lifetime, creating a solution that's environmentally friendly and real value-for-money. CoreLine DN142B recessed downlights are easy to install thanks to their standard cut-out size and push-in connectors. An Interact ready option with integrated wireless communications is also available in this family, which can be used with Interact gateways, sensors and software.

Warnings and Safety

- Do not apply excessive force to the cable & DC connector, make sure the connector clip is locked before the power is on.

Product data

General Information		Value ladder	
Light source replaceable	No	Performance	
Number of gear units	1 unit	Warranty period	5 years
Driver included	Yes	Light Technical	
Service tag	Yes	Luminous Flux	1,200 lm
Lighting Technology	LED	Saturated Red (R9)	<50
Mounting	Recessed	Correlated Color Temperature (Nom)	3000 K

CoreLine Downlight gen5

Luminous Efficacy (rated) (Nom)	120 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	- degree(s)
Light source color	830 warm white
Optic type	-
Luminaire light beam spread	60°
Unified glare rating CEN	19

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W W
Average CLO power consumption	- W W
Inrush current	14 A
Inrush time	0.001 ms
Power Consumption	9.8 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 4-pole
Cable	2 cables 0.15m with connectors 2-pole
Number of products on MCB of 16 A type B	120
Suitable for random switching	Yes
Protection class IEC	Safety class II
Total harmonic distortion	32 %

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit external (On/Off)
Control interface	-
Constant light output	No
Maximum dim level	Not applicable

Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Optical cover finish	-
Reflector Finish	Facetted reflector
Overall height	82 mm
Overall diameter	162 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	0.260 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes

ENEC mark	-
Photobiological risk	Photobiological risk group 1 @ 200mm to EN62471
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	0.5
Stroboscopic effect visibility measure (SVM)	1
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.435,0.404) SDCM≤5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L80

Sustainability Data



Sustainability rating	Unclassified
Repair class	Repair Class D, this product is not designed to be repaired.
Embedded carbon (A1-A3)	3.43 kg CO ₂ e
Product non-virgin material ratio	30.1 %
Recyclable content ratio of the finished product	31.9 %
GWP total B6 (kg CO ₂ eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO ₂ eq / kWh)
GWP total B6 (kg CO ₂ eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) /lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO ₂ eq / kWh)

Product Data


Order product name	DN142B 10S/830 PSU-E UGR19
Full product name	DN142B 10S/830 PSU-E UGR19
Full product code	872016950303899
Order code	911401551232
Material Nr. (12NC)	911401551232
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169503038
Numerator - Packs per outer box	6
EAN/UPC - Case	8720169503359

CoreLine Downlight gen5

Dimensional drawing



Photometric data



Polar Normal (separate) - 911401551232

