



GreenPerform Highbay G5

BY698X G5 LED300/CW L1W PIR WB GM

GreenPerform Highbay G5, 181 W, 31000 lm, 6500 K, Internal (no external connection), 85°

The GreenPerform Highbay G5 continues the GreenPerform family's enviable reputation for reliable performance. Not only does it deliver leading system efficacy and extended long-term quality, it also promises Unified Glare Rating (UGR) control with compact dimensions. GreenPerform Highbay G5 is also fully compatible with IoT software such as Interact, which is a scalable, future-proof control system. The family also has a series that supports cold room applications with 100% humidity and no condensation. All benefits that make this robust, optimized, and versatile family suitable for almost all industrial applications.

Product data

General Information		Operating and Electrical	
Number of gear units	1 unit	Number of light sources	1
Gear	-	Beam angle of light source	115 degree(s)
Driver included	Yes	Light source color	865 cool daylight
Light source engine type	LED	Optic type	Wide beam
Value ladder	Performance	Luminaire light beam spread	85°
Warranty period	5 years	Unified glare rating CEN	25
		Effective projected area	0 m ²
Light Technical			
Luminous Flux	31,000 lm	Input Voltage	220 to 240 V
Correlated Color Temperature (Nom)	6500 K	Line Frequency	50 or 60 Hz
Luminous Efficacy (rated) (Nom)	171 lm/W	Inrush current	54 A
Color rendering index (CRI)	80	Inrush time	0.75 ms

GreenPerform Highbay G5

Power Consumption	181 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable 0.3 m without plug
Number of products on MCB of 16 A type B	6
Suitable for random switching	Yes
Protection class IEC	Safety class I

Controls and Dimming

Dimmable	Wireless Dim - Do not use with dimmer
Control interface	Internal (no external connection)
Maximum dim level	0% (digital)

Mechanical and Housing

Housing Material	Aluminum die-cast
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Grey
Mounting device	Suspension set simple, standard
Optical cover finish	Clear
Overall length	530 mm
Overall width	393 mm
Overall height	110 mm
Dimensions (Height x Width x Depth)	110 x 393 x 530 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Clear dome
Net Weight (Piece)	4.490 kg

Approval and Application

Glow-wire test	Temperature 750 °C, duration 30 s
----------------	-----------------------------------

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	35 °C
Ambient temperature range	-30 to +50 °C

UV

UV-C radiation	0 W
UV-C irradiance defined at 0.2m	0 mW/m ²


Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.317, 0.338) SDCM<5
Power consumption tolerance	+/-10%

Product Data

Order product name	BY698X G5 LED300/CW L1W PIR WB GM
Full product name	BY698X G5 LED300/CW L1W PIR WB GM
Full product code	872110330812200
Order code	911401551445
Material Nr. (12NC)	911401551445
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103308122
Numerator - Packs per outer box	1
EAN/UPC - Case	8721103308122

Dimensional drawing



GreenPerform Highbay G5

