



GreenUp Magnetic Flex

ST307M ST P9 940 PSU-E MB

GreenUp Magnetic Flex, 9 W, 675 lm, 4000 K

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Magnetic Flex is a comprehensive product family with magnetic design which supports an easier and flexible way of installation and commissioning. It offers a complete range of options with product diversity and control availability. GreenUp Magnetic Flex gives you a plenty of flexibility to create the lighting magics.

Product data

General Information		Power Factor (Fraction)	
Light source engine type	-		0.9
Value ladder	Value	Number of products on MCB of 16 A type B	-
		Protection class IEC	Safety class III
Light Technical		Controls and Dimming	
Luminous Flux	675 lm	Dimmable	No
Correlated Color Temperature (Nom)	4000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	75 lm/W		
Color rendering index (CRI)	>90	Mechanical and Housing	
Light source color	940 neutral white	Housing Material	Aluminum extruded
		Optical cover material	Polycarbonate
Operating and Electrical		Housing Color	Black
Input Voltage	48 V	Optical cover finish	Smoke
Line Frequency	- Hz	Ingress protection code	IP20 [Finger-protected]
Inrush current	0.15 A	Mech. impact protection code	IK03 [0.3 J]
Power Consumption	9 W	Optical cover type	Polycarbonate micro lens optic

GreenUp Magnetic Flex

Net Weight (Piece)	0.194 kg
Approval and Application	
CE mark	No
Ambient temperature range	-20 to +40 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Full product name	ST307M ST P9 940 PSU-E MB
Full product code	872016953412499
Order code	53412499
Material Nr. (12NC)	911401554502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169534124
Numerator - Packs per outer box	20
EAN/UPC - Case	8720169545618

Product Data	
Order product name	ST307M ST P9 940 PSU-E MB

Dimensional drawing

