



GreenUp Magnetic Flex

ST307M ST P9 930 PSR-E 1-10V NB

GreenUp Magnetic Flex, 9 W, 470 lm, 3000 K, depends on driver (1-10V, DALI...)

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Magnetic Flex is a comprehensive product family with magnetic design which supports an easier and flexible way of installation and commissioning. It offers a complete range of options with product diversity and control availability. GreenUp Magnetic Flex gives you a plenty of flexibility to create the lighting magics.

Product data

General Information			
Light source engine type	LED	Inrush current	0.15 A
Value ladder	Value	Power Consumption	9 W
Light Technical		Power Factor (Fraction)	0.9
Luminous Flux	470 lm	Number of products on MCB of 16 A type B	-
Correlated Color Temperature (Nom)	3000 K	Protection class IEC	Safety class III
Luminous Efficacy (rated) (Nom)	46 lm/W	Controls and Dimming	
Color rendering index (CRI)	>90	Dimmable	Yes
Light source color	930 warm white	Control interface	depends on driver (1-10V, DALI...)
Unified glare rating CEN	19	Mechanical and Housing	
Operating and Electrical		Housing Material	Aluminum extruded
Input Voltage	24 V	Optical cover material	Polycarbonate
Line Frequency	- Hz	Housing Color	Black
		Optical cover finish	Smoke

GreenUp Magnetic Flex

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Polycarbonate micro lens optic
Net Weight (Piece)	0.194 kg

Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	ST307M ST P9 930 PSR-E 1-10V NB
Full product name	ST307M ST P9 930 PSR-E 1-10V NB
Full product code	872016952637299
Order code	911401557102
Material Nr. (12NC)	911401557102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169526372
Numerator - Packs per outer box	20
EAN/UPC - Case	8720169537866

