



# PowerBalance G4

## RC650B LED40S9 TWH W60L60

PowerBalance G4, 131.7 lm/W, 930 warm white and 965 cool daylight, DALI

PowerBalance G4 (RC650 range) is a complete office lighting family which creates a modern, flexible, and comfortable environment that fosters creativity and innovation. It provides multiple control options (Interact office, Interact pro, POE) to make your office energy efficient and easy to manage.

### Product data

General Information	
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
Service tag	Yes
Value ladder	Specification
Warranty period	3 years
Light Technical	
Luminous Flux	3,950 lm
Correlated Color Temperature (Nom)	-
Luminous Efficacy (rated) (Nom)	131.7 lm/W
Color rendering index (CRI)	>90
Beam angle of light source	120 degree(s)
Light source color	930 warm white and 965 cool daylight
Optic type	Reflector
Luminaire light beam spread	100° x 100°
Unified glare rating CEN	16

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Initial CLO power consumption	N.A. W
Average CLO power consumption	N.A. W
Inrush current	12 A
Inrush time	50 ms
Power Consumption	30 W
Power Factor (Fraction)	0.9
Connection	Screw connection block 3-pole
Cable	-
Number of products on MCB of 16 A type B	80
Suitable for random switching	No
Protection class IEC	Safety class II
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	DALI

## PowerBalance G4

Constant light output	No
Maximum dim level	1%

### Mechanical and Housing

Housing Material	Steel
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Textured
Overall length	597 mm
Overall width	597 mm
Overall height	70 mm
Dimensions (Height x Width x Depth)	70 x 597 x 597 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Polycarbonate
Net Weight (Piece)	4.000 kg

### Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes

ENEC mark	-
EU RoHS compliant	Yes
Ambient temperature range	-20 to +40 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
Median useful life L80B50	50,000 hour(s)
Median useful life L90B50	33,817 hour(s)

### Product Data

Order product name	RC650B LED40S9 TWH W60L60
Full product name	RC650B LED40S9 TWH W60L60
Full product code	911401557861
Order code	911401557861
Material Nr. (12NC)	911401557861
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

## Dimensional drawing

