



GreenUp Magnetic Flex

ST307M GL P15 940 PSR-E 1-10V OP

GreenUp Magnetic Flex, 15 W, 940 neutral white, depends on driver (1-10V, DALI...), IP20 | Finger-protected

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Magnetic Flex is a comprehensive product family with magnetic design which supports an easier and flexible way of installation and commissioning. It offers a complete range of options with product diversity and control availability. GreenUp Magnetic Flex gives you a plenty of flexibility to create the lighting magics.

Product data

| General Information | | | |
|------------------------------------|-------------------|--|------------------------------------|
| Light source engine type | LED | Inrush current | 0.15 A |
| Value ladder | Value | Power Consumption | 15 W |
| Light Technical | | Power Factor (Fraction) | 0.9 |
| Luminous Flux | 810 lm | Number of products on MCB of 16 A type B | - |
| Correlated Color Temperature (Nom) | 4000 K | Protection class IEC | Safety class III |
| Luminous Efficacy (rated) (Nom) | 54 lm/W | Controls and Dimming | |
| Color rendering index (CRI) | >90 | Dimmable | Yes |
| Light source color | 940 neutral white | Control interface | depends on driver (1-10V, DALI...) |
| Unified glare rating CEN | 34 | Mechanical and Housing | |
| Operating and Electrical | | Housing Material | Aluminum extruded |
| Input Voltage | 24 V | Optical cover material | Polycarbonate |
| Line Frequency | - Hz | Housing Color | Black |
| | | Optical cover finish | Smoke |

GreenUp Magnetic Flex

| | |
|------------------------------|--------------------------------|
| Ingress protection code | IP20 [Finger-protected] |
| Mech. impact protection code | IK03 [0.3 J] |
| Optical cover type | Polycarbonate micro lens optic |
| Net Weight (Piece) | 0.196 kg |

Approval and Application

| | |
|---------------------------|---------------|
| CE mark | No |
| Ambient temperature range | -20 to +40 °C |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|--------|
| Luminous flux tolerance | +/-10% |
| Power consumption tolerance | +/-10% |

Product Data

| | |
|---------------------------------|----------------------------------|
| Order product name | ST307M GL P15 940 PSR-E 1-10V OP |
| Full product name | ST307M GL P15 940 PSR-E 1-10V OP |
| Full product code | 872016951792999 |
| Order code | 911401558802 |
| Material Nr. (12NC) | 911401558802 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8720169517929 |
| Numerator - Packs per outer box | 20 |
| EAN/UPC - Case | 8720169518537 |

Dimensional drawing

