



# GreenUp Magnetic Flex

## ST307M SS P5 940 PSR-E 1-10V NB

GreenUp Magnetic Flex, 90 lm/W, 940 neutral white, depends on driver (1-10V, DALI...)

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Magnetic Flex is a comprehensive product family with magnetic design which supports an easier and flexible way of installation and commissioning. It offers a complete range of options with product diversity and control availability. GreenUp Magnetic Flex gives you a plenty of flexibility to create the lighting magics.

### Product data

General Information			
Light source engine type	LED	Inrush current	0.15 A
Value ladder	Value	Power Consumption	5 W
Light Technical		Power Factor (Fraction)	0.9
Luminous Flux	450 lm	Number of products on MCB of 16 A type B	-
Correlated Color Temperature (Nom)	4000 K	Protection class IEC	Safety class III
Luminous Efficacy (rated) (Nom)	90 lm/W	Controls and Dimming	
Color rendering index (CRI)	>90	Dimmable	Yes
Light source color	940 neutral white	Control interface	depends on driver (1-10V, DALI...)
Unified glare rating CEN	19	Mechanical and Housing	
Operating and Electrical		Housing Material	Aluminum extruded
Input Voltage	24 V	Optical cover material	Polycarbonate
Line Frequency	- Hz	Housing Color	Black
		Optical cover finish	Smoke

## GreenUp Magnetic Flex

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Polycarbonate micro lens optic
Net Weight (Piece)	0.365 kg

### Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

### Product Data

Order product name	ST307M SS P5 940 PSR-E 1-10V NB
Full product name	ST307M SS P5 940 PSR-E 1-10V NB
Full product code	872016952298599
Order code	911401559202
Material Nr. (12NC)	911401559202
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169522985
Numerator - Packs per outer box	16
EAN/UPC - Case	8720169534476

