



# SlimBalance G3

## RC570B LED50/9TW L150W6 SD PSD

SlimBalance G3, 126 lm/W, Tunable white, DALI

SlimBalance G3 SP570P is a flexible linear office offer which fits a variety of spaces like office, education. It offers flexible width of 35/60/90/120mm and length of 600/1200/1500mm to fit multiple applications. Geometric shapes help further create differentiated space. By means of its special designed structure, it offers quick and easy installation and maintenance. UGR19 is available for certain types through customized solution to provide a better visual comfort office environment.

### Product data

General Information		Power Factor (Fraction)		0.9
Light source engine type	LED	Number of products on MCB of 16 A type B		16
Service tag	Yes	Protection class IEC		Safety class I
Value ladder	Performance	<b>Controls and Dimming</b>		
<b>Light Technical</b>		Dimmable	DALI	
Luminous Flux	5,170 lm	Control interface	DALI	
Correlated Color Temperature (Nom)	Tunable White	<b>Mechanical and Housing</b>		
Luminous Efficacy (rated) (Nom)	126 lm/W	Housing Material	Aluminum Alloy	
Color rendering index (CRI)	>90	Optical cover material	Polycarbonate	
Beam angle of light source	116 degree(s)	Housing Color	White RAL 9003	
Light source color	Tunable white	Optical cover finish	Frosted	
Unified glare rating CEN	27	Overall length	1,530 mm	
<b>Operating and Electrical</b>		Overall width	70 mm	
Input Voltage	220-240 V	Overall height	80 mm	
Line Frequency	50 or 60 Hz	Dimensions (Height x Width x Depth)	80 x 70 x 1530 mm	
Inrush current	29.6 A	Ingress protection code	IP20 [Finger-protected]	
Power Consumption	41 W	Mech. impact protection code	IK03 [0.3 J]	

## SlimBalance G3

Optical cover type	Polycarbonate bowl/cover frosted
Net Weight (Piece)	3.000 kg

### Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +40 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Initial chromaticity	SDCM<=4
Power consumption tolerance	+/-10%

### Product Data

Order product name	RC570B LED50/9TW L150W6 SD PSD
Full product name	RC570B LED50/9TW L150W6 SD PSD
Order code	911401569342
Material Nr. (12NC)	911401569342
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

## Dimensional drawing

