



Emergency Light LED Exit Sign

EM132C Emergency Razor with up legend

Emergency Light LED Exit Sign, 2.2 W, 19 lm, 7000 K, Clear, IP20 | Finger-protected

Safety is important for building owners, and therefore having proper emergency lighting in place is a major concern for them. The Emergency exit sign offers an easy solution for stand-alone emergency lighting, with maintained mode and various installation methods which are suitable for different applications. The lithium battery (LiFePO4) has many advantages over nickel-based products, as it has a longer lifetime, better discharge behaviors, is produced in a more welfare friendly way and can be recycled.

Product data

General Information		Beam angle of light source	
Number of gear units	-		- degree(s)
Gear	-	Light source color	765 cool daylight
Driver included	Yes	Optic type	-
Light source engine type	LED	Luminaire light beam spread	-
Value ladder	Value	Unified glare rating CEN	22
Warranty period	1 years		
Light Technical		Operating and Electrical	
Luminous Flux	19 lm	Input Voltage	220 to 240 V
Correlated Color Temperature (Nom)	7000 K	Line Frequency	50 to 60 Hz
Luminous Efficacy (rated) (Nom)	23.7 lm/W	Inrush current	5.36 A
Color rendering index (CRI)	70	Inrush time	0.0016 ms
Number of light sources	1	Power Consumption	2.2 W
		Power Factor (Fraction)	0.35
		Connection	Push-in connector 3-pole

Emergency Light LED Exit Sign

Cable	-
Number of products on MCB of 16 A type B	245
Suitable for random switching	No
Protection class IEC	-
Controls and Dimming	
Dimmable	No
Control interface	-
Maximum dim level	Not applicable
Mechanical and Housing	
Housing Material	Plastic
Reflector material	-
Optic material	-
Optical cover material	Acrylate
Housing Color	Gray
Mounting device	-
Optical cover finish	Clear
Overall length	313 mm
Overall width	42 mm
Overall height	212 mm
Dimensions (Height x Width x Depth)	212 x 42 x 313 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Acrylic bowl/cover
Net Weight (Piece)	0.520 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	-
EU RoHS compliant	No
Performance ambient temperature Tq	25 °C
Ambient temperature range	0 to +45 °C


Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Initial chromaticity	-
Power consumption tolerance	+/-10%

Product Data

Order product name	EM132C Emergency Razor with up legend
Full product name	EM132C Emergency Razor with up legend
Full product code	872110332025499
Order code	32025499
Material Nr. (12NC)	911401587043
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103320254
Numerator - Packs per outer box	10
EAN/UPC - Case	8721103320278

Dimensional drawing



Emergency Light LED Exit Sign

