



# Emergency Light LED Pathfinder

## EM152B Emergency Spitfire

Emergency Light LED Pathfinder, 165 lm/W, 765 cool daylight

Safety is important for building owners, and therefore having proper emergency lighting in place is a major concern for them. The Emergency pathfinder offers an easy solution for stand-alone emergency lighting, with non-maintained mode and self-test function. The lithium battery (LiFePO4) has many advantages over nickel-based products, as it has a longer lifetime, better discharge behaviors, is produced in a more welfare friendly way and can be recycled.

### Product data

General Information		Optic type	
Number of gear units	-	Optic type	-
Gear	-	Luminaire light beam spread	-
Driver included	Yes	Unified glare rating CEN	22
Light source engine type	LED	Operating and Electrical	
Value ladder	Value	Input Voltage	220 to 240 V
Warranty period	1 years	Line Frequency	50 to 60 Hz
Light Technical		Inrush current	4.6 A
Luminous Flux	300 lm	Inrush time	0.0048 ms
Correlated Color Temperature (Nom)	6500 K	Power Consumption	1.6 W
Luminous Efficacy (rated) (Nom)	165 lm/W	Power Factor (Fraction)	0.2
Color rendering index (CRI)	70	Connection	-
Number of light sources	1	Cable	Cable 0.3 m without plug
Beam angle of light source	- degree(s)	Number of products on MCB of 16 A type B	284
Light source color	765 cool daylight	Suitable for random switching	No

# Emergency Light LED Pathfinder

Protection class IEC	-
----------------------	---

## Controls and Dimming

Dimmable	No
Control interface	-
Maximum dim level	Not applicable

## Mechanical and Housing

Housing Material	Plastic
Reflector material	-
Optic material	-
Optical cover material	Polycarbonate
Housing Color	Gray
Mounting device	-
Optical cover finish	Clear
Overall height	38.3 mm
Overall diameter	95 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Acrylic bowl/cover
Net Weight (Piece)	0.320 kg

## Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
----------------	-----------------------------------

CE mark	Yes
ENEC mark	-
EU RoHS compliant	No
Performance ambient temperature Tq	25 °C
Ambient temperature range	0 to +45 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Initial chromaticity	-
Power consumption tolerance	+/-10%

## Product Data

Order product name	EM152B Emergency Spitfire
Full product name	EM152B Emergency Spitfire
Full product code	872110330467499
Order code	911401588043
Material Nr. (12NC)	911401588043
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103304674
Numerator - Packs per outer box	20
EAN/UPC - Case	8721103304704

## Dimensional drawing

