



# GreenUp Round Highbay

## BY518P SE LED50/NW PSU WB

GreenUp Round Highbay, 30.5 W, 5000 lm, 4000 K, 90°

The GreenUp Round Highbay range of luminaires provides the optimal balance between basic performance and price. The family covers a wide product range with a variety of options, competitive specifications, and long-term quality and reliability. The range is suitable for most industrial applications.

### Product data

General Information	
Number of gear units	1 unit
Gear	-
Driver included	Yes
Light source engine type	LED
Value ladder	Performance
Warranty period	3 years
Light Technical	
Luminous Flux	5,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	163 lm/W
Color rendering index (CRI)	>80
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	840 neutral white
Optic type	Wide beam
Luminaire light beam spread	90°

Unified glare rating CEN	26
Effective projected area	0.06 m²
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Inrush current	11.5 A
Inrush time	0.75 ms
Power Consumption	30.5 W
Power Factor (Fraction)	0.95
Connection	-
Cable	Cable 0.3 m without plug 3-pole
Number of products on MCB of 16 A type B	11
Suitable for random switching	No
Protection class IEC	Safety class I
Controls and Dimming	
Dimmable	No

## GreenUp Round Highbay

Control interface	-
Maximum dim level	Not applicable

### Mechanical and Housing

Housing Material	Aluminum
Reflector material	Aluminum
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Grey
Mounting device	Suspension set simple, standard
Optical cover finish	Clear
Overall height	93 mm
Overall diameter	273 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Lens
Net Weight (Piece)	1.390 kg

### Approval and Application

Glow-wire test	-
Flammability mark	-
CE mark	Yes

ENEC mark	-
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	35 °C
Ambient temperature range	-30 to +45 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.375) SDCM<5
Power consumption tolerance	+/-10%

### Product Data

Order product name	BY518P SE LED50/NW PSU WB
Full product name	BY518P SE LED50/NW PSU WB
Order code	911401588745
Material Nr. (12NC)	911401588745
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Dimensional drawing

