



GreenPerform Canopy Mini500 G4

BBP500 G4 LED140/NW PSU S-MB

GreenPerform Canopy Mini500 G4, 91 W, 14079 lm, 4000 K

The Philips GreenPerform Canopy Mini500 Gen4 lives up to the GreenPerform family's enviable reputation for reliable performance. Not only does this next-generation, energy-saving LED deliver leading system efficacy and extended long-term quality, it also offers a versatile selection of optics, connectivity, controls and installation options. So you can create the ideal lighting conditions for any space, at any time. The GreenPerform Canopy portfolio also includes a series that is ideal for canopy lighting in food applications. For professionals who demand high-performance, connected lighting for their lighting installations, this robust, optimized, and versatile family of LED canopy luminaires is the perfect choice for both indoor and outdoor canopy applications.

Product data

General Information		Operating and Electrical	
Light source engine type	LED	Input Voltage	220-240 V
Service tag	Yes	Line Frequency	50 to 60 Hz
Value ladder	Performance	Inrush current	35.4 A
Light Technical		Power Consumption	91 W
Luminous Flux	14,079 lm	Power Factor (Fraction)	0.95
Correlated Color Temperature (Nom)	4000 K	Number of products on MCB of 16 A type B	8
Luminous Efficacy (rated) (Nom)	155 lm/W	Protection class IEC	Safety class I
Color rendering index (CRI)	>80	Controls and Dimming	
Light source color	840 neutral white	Dimmable	No

GreenPerform Canopy Mini500 G4

Control interface	-
-------------------	---

Mechanical and Housing

Housing Material	Aluminium die-cast ADC1 - alloy grade (EN AC-47100)
Optical cover material	Tempered glass
Housing Color	White
Optical cover finish	Clear
Overall length	423 mm
Overall width	400 mm
Overall height	96 mm
Dimensions (Height x Width x Depth)	96 x 400 x 423 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Optical cover type	Clear glass
Net Weight (Piece)	4.790 kg

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
-------------------	---

CE mark	Yes
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BBP500 G4 LED140/NW PSU S-MB
Full product name	BBP500 G4 LED140/NW PSU S-MB
Full product code	872016954718600
Order code	54718600
Material Nr. (12NC)	911401594432
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169547186
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169547186

Dimensional drawing

