



GreenPerform Canopy Mini500 G4

BBP500 G4 LED85/CW PSD S-WB

GreenPerform Canopy Mini500 G4, 58 W, 8496 lm, 6500 K, DALI

The Philips GreenPerform Canopy Mini500 Gen4 lives up to the GreenPerform family's enviable reputation for reliable performance. Not only does this next-generation, energy-saving LED deliver leading system efficacy and extended long-term quality, it also offers a versatile selection of optics, connectivity, controls and installation options. So you can create the ideal lighting conditions for any space, at any time. The GreenPerform Canopy portfolio also includes a series that is ideal for canopy lighting in food applications. For professionals who demand high-performance, connected lighting for their lighting installations, this robust, optimized, and versatile family of LED canopy luminaires is the perfect choice for both indoor and outdoor canopy applications.

Product data

General Information		Light source color	
Light source engine type	LED		865 cool daylight
Service tag	Yes	Operating and Electrical	
Value ladder	Performance	Input Voltage	220-240 V
		Line Frequency	50 to 60 Hz
		Inrush current	35.4 A
Light Technical		Power Consumption	58 W
Luminous Flux	8,496 lm	Power Factor (Fraction)	0.9
Correlated Color Temperature (Nom)	6500 K	Number of products on MCB of 16 A type B 8	
Luminous Efficacy (rated) (Nom)	147 lm/W	Protection class IEC	Safety class I
Color rendering index (CRI)	>80		

GreenPerform Canopy Mini500 G4

Controls and Dimming

Dimmable	DALI
Control interface	DALI

Mechanical and Housing

Housing Material	Aluminium die-cast ADC1 - alloy grade (EN AC-47100)
Optical cover material	Tempered glass
Housing Color	White
Optical cover finish	Clear
Overall length	427 mm
Overall width	400 mm
Overall height	115 mm
Dimensions (Height x Width x Depth)	115 x 400 x 427 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Optical cover type	Clear glass
Net Weight (Piece)	7.190 kg

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
-------------------	---

CE mark	Yes
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BBP500 G4 LED85/CW PSD S-WB
Full product name	BBP500 G4 LED85/CW PSD S-WB
Full product code	872016954800800
Order code	54800800
Material Nr. (12NC)	911401595832
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169548008
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169548008

Dimensional drawing

