



GreenPerform Canopy Mini500 G4

BBP500 G4 LED140/NW PSD S-WB

GreenPerform Canopy Mini500 G4, 96 W, 14079 lm, 4000 K, DALI

The Philips GreenPerform Canopy Mini500 Gen4 lives up to the GreenPerform family's enviable reputation for reliable performance. Not only does this next-generation, energy-saving LED deliver leading system efficacy and extended long-term quality, it also offers a versatile selection of optics, connectivity, controls and installation options. So you can create the ideal lighting conditions for any space, at any time. The GreenPerform Canopy portfolio also includes a series that is ideal for canopy lighting in food applications. For professionals who demand high-performance, connected lighting for their lighting installations, this robust, optimized, and versatile family of LED canopy luminaires is the perfect choice for both indoor and outdoor canopy applications.

Product data

General Information		Light source color	
Light source engine type	LED	840 neutral white	
Service tag	Yes	Operating and Electrical	
Value ladder	Performance	Input Voltage	220-240 V
Light Technical		Line Frequency	50 to 60 Hz
Luminous Flux	14,079 lm	Inrush current	35.4 A
Correlated Color Temperature (Nom)	4000 K	Power Consumption	96 W
Luminous Efficacy (rated) (Nom)	147 lm/W	Power Factor (Fraction)	0.95
Color rendering index (CRI)	>80	Number of products on MCB of 16 A type B 8	
		Protection class IEC	Safety class I

GreenPerform Canopy Mini500 G4

Controls and Dimming

Dimmable	DALI
Control interface	DALI

Mechanical and Housing

Housing Material	Aluminium die-cast ADC1 - alloy grade (EN AC-47100)
Optical cover material	Tempered glass
Housing Color	White
Optical cover finish	Clear
Overall length	427 mm
Overall width	400 mm
Overall height	115 mm
Dimensions (Height x Width x Depth)	115 x 400 x 427 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Optical cover type	Clear glass
Net Weight (Piece)	7.190 kg

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
-------------------	---

CE mark	Yes
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BBP500 G4 LED140/NW PSD S-WB
Full product name	BBP500 G4 LED140/NW PSD S-WB
Full product code	872016954765000
Order code	911401596732
Material Nr. (12NC)	911401596732
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169547650
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169547650

Dimensional drawing

