



LuxSpace Pro

DN591B LED23/840 P17PSD D150 WB G2

LuxSpace Pro, 17.4 W, 2260 lm, 4000 K, DALI

Philips LuxSpace Pro builds on the LuxSpace family's reputation for superb performance, extremely low energy use, high visual comfort and appearance design. This next generation of reliable LED downlights comes in an elegant design with a deep, recessed architecture and increased reflector depth to highlight the smallest of details. LuxSpace Pro is also a shining example of versatility. This energy-saving LED downlight is available in a comprehensive range of configurations from 450 to 8,000 lumen, 3inch to 8inch, with the option to choose fixed, dimmable, or Interact Ready variants. This makes LuxSpace Pro the perfect 'mix and match' solution for potentially broad and extended applications that require different lighting ambiances, with one cohesive luminaire look and feel.

Product data

| General Information | | Operating and Electrical | |
|------------------------------------|---|--|-----------------|
| Light source engine type | LED | Input Voltage | 220-240 V |
| Service tag | Yes | Line Frequency | 50 or 60 Hz |
| Value ladder | Specification | Inrush current | 16.5 A |
| Light Technical | | Inrush time | 177 ms |
| Luminous Flux | 2,260 lm | Power Consumption | 17.4 W |
| Correlated Color Temperature (Nom) | 4000 K | Power Factor (Fraction) | 0.9 |
| Luminous Efficacy (rated) (Nom) | 130 lm/W | Number of products on MCB of 16 A type B | 36 |
| Color rendering index (CRI) | 80 | Protection class IEC | Safety class II |
| Light source color | 840 neutral white | Controls and Dimming | |
| Optic type | High-reflective metal reflector Wide beam 40 to 80 degrees | Dimmable | Yes |
| Unified glare rating CEN | 18 | Control interface | DALI |
| | | Maximum dim level | 1% |

LuxSpace Pro

Mechanical and Housing

| | |
|------------------------------|-------------------------|
| Housing Material | Aluminum Alloy |
| Optical cover material | Polycarbonate |
| Housing Color | White |
| Optical cover finish | Frosted |
| Ingress protection code | IP20 [Finger-protected] |
| Mech. impact protection code | IK03 [0.3 J] |
| Optical cover type | Polycarbonate Diffuser |
| Net Weight (Piece) | 0.610 kg |

Approval and Application

| | |
|---------------------------|-----------------|
| CE mark | Yes |
| Ambient temperature range | -20 °C to 40 °C |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|--------|
| Luminous flux tolerance | +/-10% |
| Power consumption tolerance | +/-10% |

Product Data

| | |
|---------------------------------|------------------------------------|
| Order product name | DN591B LED23/840 P17PSD D150 WB G2 |
| Full product name | DN591B LED23/840 P17PSD D150 WB G2 |
| Order code | 911401597543 |
| Material Nr. (12NC) | 911401597543 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |

Dimensional drawing

