



LuxSpace Pro

DN595B LED61/830 P47PSD D200 VWB-M G2

LuxSpace Pro, 46.6 W, 6035 lm, 3000 K, DALI

Philips LuxSpace Pro builds on the LuxSpace family's reputation for superb performance, extremely low energy use, high visual comfort and appearance design. This next generation of reliable LED downlights comes in an elegant design with a deep, recessed architecture and increased reflector depth to highlight the smallest of details. LuxSpace Pro is also a shining example of versatility. This energy-saving LED downlight is available in a comprehensive range of configurations from 450 to 8,000 lumen, 3inch to 8inch, with the option to choose fixed, dimmable, or Interact Ready variants. This makes LuxSpace Pro the perfect 'mix and match' solution for potentially broad and extended applications that require different lighting ambiances, with one cohesive luminaire look and feel.

Product data

General Information		Operating and Electrical	
Light source engine type	LED	Input Voltage	220-240 V
Service tag	Yes	Line Frequency	50 or 60 Hz
Value ladder	Specification	Inrush current	5.5 A
		Inrush time	55 ms
		Power Consumption	46.6 W
		Power Factor (Fraction)	0.95
		Number of products on MCB of 16 A type B	27
		Protection class IEC	Safety class II
Light Technical		Controls and Dimming	
Luminous Flux	6,035 lm	Dimmable	Yes
Correlated Color Temperature (Nom)	3000 K	Control interface	DALI
Luminous Efficacy (rated) (Nom)	130 lm/W	Maximum dim level	1%
Color rendering index (CRI)	80		
Light source color	830 warm white		
Optic type	High-efficiency reflector medium beam		
Unified glare rating CEN	28		

LuxSpace Pro

Mechanical and Housing

Housing Material	Aluminum Alloy
Optical cover material	Polycarbonate
Housing Color	White
Optical cover finish	Frosted
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Polycarbonate Diffuser
Net Weight (Piece)	1.260 kg

Approval and Application

CE mark	Yes
Ambient temperature range	-20 °C to 40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Power consumption tolerance	+/-10%
-----------------------------	--------

Product Data

Order product name	DN595B LED61/830 P47PSD D200 VWB-M G2
Full product name	DN595B LED61/830 P47PSD D200 VWB-M G2
Order code	911401599443
Material Nr. (12NC)	911401599443
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

