



FlowPad

BWP603 LED284/NW 170W DTA C

FlowPad, 28300 lm, 170 W, 740 neutral white, 148° x 88°, depends on driver (1-10V, DALI...), Safety class I, Mounting bracket adjustable

Municipalities value energy savings more than ever, as energy price hikes put increasing pressure on budgets. Tunnel lighting consumes substantial energy, so large-scale upgrades to energy-efficient LED tunnel lights are essential to cities' cost-saving efforts. FlowPad has been upgraded to minimize costs while maximizing efficacy, safety, and functionality. And the best part — FlowPad offers big light window with professional photometric, so it ensures safe and comfortable lighting in tunnels. These tunnel lights not only look good, they also offer excellent performance. Future-proof technology combines with high efficacy, innovative design, and smart connectivity in a light that makes your tunnels look brighter and better.

Product data

General Information		Beam angle of light source	
Number of gear units	-	Beam angle of light source	116 degree(s)
Driver included	No	Light source color	740 neutral white
Light source engine type	LED	Optic type	Very wide beam
Service tag	Yes	Luminaire light beam spread	148° x 88°
Value ladder	Specification	Effective projected area	0.135 m²
Light Technical		Operating and Electrical	
Luminous Flux	28,300 lm	Input Voltage	200-250 V
Correlated Color Temperature (Nom)	4000 K	Line Frequency	0 Hz
Luminous Efficacy (rated) (Nom)	166 lm/W	Power Consumption	170 W
Color rendering index (CRI)	70	Power Factor (Fraction)	0.9
		Connection	Connection unit 3-pole

FlowPad

Cable	Cable with connector 3-pole
Number of products on MCB of 16 A type B	-
Protection class IEC	Safety class I
Controls and Dimming	
Dimmable	Yes
Control interface	depends on driver (1-10V, DALI...)
Mechanical and Housing	
Housing Material	Aluminum extruded
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Grey
Mounting device	Mounting bracket adjustable
Optical cover finish	Clear
Overall length	529 mm
Overall width	322 mm
Overall height	180 mm
Dimensions (Height x Width x Depth)	180 x 322 x 529 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Glass
Net Weight (Piece)	6.890 kg

Approval and Application

Glow-wire test	-
Flammability mark	-
CE mark	Yes
ENEC mark	-
EU RoHS compliant	Yes
Performance ambient temperature Tq	50 °C
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Initial chromaticity	0.3818,0.3797
Power consumption tolerance	+/-10%

Product Data

Order product name	BWP603 LED284/NW 170W DTA C
Full product name	BWP603 LED284/NW 170W DTA C
Order code	911401606509
Material Nr. (12NC)	911401606509
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

