



Tango G4 LED Flood

BVP433 LED384/CW 300W AMB CM GM

Tango G4 LED Flood, 38400 lm, 300 W, 757 cool white, Safety class I

Philips Tango G4 LED flood lighting is the 4th generation of the Tango LED family. A new range lighting that delivers higher efficacy and has an optimized windage area, and less weight thanks to its technical design. This product introduction is the ideal solution for a wide range of area lighting and recreational sports lighting applications. It incorporates the latest LED light source, one-piece optical system, heat sink and driver into a compact and robust housing that meets globally-recognized safety standards. Its specially-designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. Powered by LED technology, Tango G4 LED floodlights deliver superior performance and a longer lifetime, bringing area lighting to a whole new level.

Warnings and Safety

- please pay attention to the mounting instructions

Product data

General Information		Color rendering index (CRI)		>70
Driver included	Yes	Light source color	757 cool white	
Service tag	Yes	Operating and Electrical		
Lighting Technology	LED	Input Voltage	220 to 240 V	
Value ladder	Performance	Line Frequency	50 or 60 Hz	
Light Technical		Power Consumption	300 W	
Luminous Flux	38,400 lm	Power Factor (Fraction)	0.9	
Correlated Color Temperature (Nom)	5700 K	Connection	Flying leads/wires	
Luminous Efficacy (rated) (Nom)	128 lm/W	Cable	Cable 1.5 m without plug	

Tango G4 LED Flood

Number of products on MCB of 16 A type B 6	
Protection class IEC	Safety class I
Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing Material	Aluminum die cast
Optical cover material	Polycarbonate
Housing Color	Gray
Overall length	523 mm
Overall width	559 mm
Overall height	71 mm
Dimensions (Height x Width x Depth)	71 x 559 x 523 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Polycarbonate bowl/cover
Net Weight (Piece)	12.160 kg

Approval and Application

CE mark	Yes
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BVP433 LED384/CW 300W AMB CM GM
Full product name	BVP433 LED384/CW 300W AMB CM GM
Full product code	871951454062000
Order code	54062000
Material Nr. (12NC)	911401607907
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514540620
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514540620

Dimensional drawing

