



Tango Pro

BVP563 LED311/740 220W EP SAWB ANZ

Tango Pro, 31100 lm, 220 W, 740 neutral white, depends on driver (1-10V, DALI...), Safety class I

Philips Tango Pro LED floodlight is the fifth generation of the Philips Tango LED floodlight. Tango Pro takes efficiency to the next level, delivering industry-best efficiency in a compact but elegant design. The luminaire can be applied in a versatile range of applications, from area lighting to recreational sports facilities. The LED driver comes in compact and robust housing that meets globally recognized safety standards. Its specially designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. The modular, streamlined luminaire silhouette offers a visually balanced design. Philips Tango Pro LED floodlight is engineered to create brighter and safer environments. Powered by the latest LED technology, Tango Pro delivers superior performance in both light distribution and UltraEfficiency 170lm/W and up to 200lm/W. The long luminaire lifetime and recyclable materials supports your efforts to meet sustainability targets.

Warnings and Safety

- For coastline applications, 2,000 hours (or above) MSP recommended (liability for wear-and-tear damages exempted)
- Not suitable for chemical industrial areas
- Not suitable for installation on moving objects

Product data

General Information		Correlated Color Temperature (Nom)	
Driver included	Yes		4000 K
Service tag	Yes	Luminous Efficacy (rated) (Nom)	141 lm/W
Value ladder	Performance	Color rendering index (CRI)	70
		Light source color	740 neutral white
		Effective projected area	0.18 m ²
Light Technical			
Luminous Flux	31,100 lm		

Tango Pro

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	78 A
Inrush time	0.238 ms
Power Consumption	220 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable 1.5 m without plug
Number of products on MCB of 16 A type B 4	
Protection class IEC	Safety class I

Controls and Dimming

Dimmable	1-10V
Control interface	depends on driver (1-10V, DALI...)

Mechanical and Housing

Housing Material	Aluminium die-cast ADC1 - alloy grade (EN AC-47100)
Optical cover material	Polycarbonate
Housing Color	RAL7040
Overall length	512 mm
Overall width	437 mm
Overall height	77 mm
Overall diameter	621 mm

Dimensions (Height x Width x Depth)	77 x 437 x 512 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [6 J]
Optical cover type	Polycarbonate
Net Weight (Piece)	7.850 kg

Approval and Application

Flammability mark	-
CE mark	Yes
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Initial chromaticity	(0.382 0.380) SDCM<5
Power consumption tolerance	+/-10%

Product Data

Order product name	BVP563 LED31/740 220W EP SAWB ANZ
Full product name	BVP563 LED31/740 220W EP SAWB ANZ
Order code	911401609309
Material Nr. (12NC)	911401609309
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

