



CoreLine Highbay Gen5

BY121P G5 LED200S/865 PSD WB

CoreLine Highbay Gen5, 126 W, 20500 lm, 6500 K, DALI, Wide beam, IP65, IK08

CoreLine Highbay Gen5 delivers on the CoreLine promise of innovative, easy-to-use and high-quality luminaires. A reliable, highly-efficient luminaire with a very long-lifetime, it delivers great energy savings and requires less maintenance. At the same time, CoreLine Highbay is very easy to handle. The luminaire can be installed on your existing grid and the electrical connection is a straightforward task, with no need to open the luminaire and an external IP65 connector. With a choice of two beam angles: narrow and wide beam, you can adjust your lighting plan to suit your exact needs. This range also includes Interact Ready luminaires with integrated wireless communications and integrated movement and daylight sensors. So CoreLine Highbay Gen5 is ready to be used with any Interact connected lighting system.

Product data

General Information		Light Technical	
Light source replaceable	No	Luminous Flux	20,500 lm
Number of gear units	1 unit	Saturated Red (R9)	<50
Driver included	Yes	Correlated Color Temperature (Nom)	6500 K
Service tag	Yes	Luminous Efficacy (rated) (Nom)	163 lm/W
Lighting Technology	LED	Color rendering index (CRI)	>80
Value ladder	Performance	Light source color	865 cool daylight
Warranty period	5 years	Optic type	Wide beam
		Luminaire light beam spread	85° x 85°

CoreLine Highbay Gen5

Unified glare rating CEN	25
--------------------------	----

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	126 W
Power Factor (Fraction)	0.95
Connection	Connection unit 3-pole
Cable	Cable 0.3 m with connector 3-pole
Number of products on MCB of 16 A type B	8
Suitable for random switching	Yes
Protection class IEC	Safety class I
Total harmonic distortion	15 %

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
DALI Standard	DALI-2™
Maximum dim level	10%

Mechanical and Housing

Housing Material	Aluminum die-cast
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	Grey
Optical cover finish	Clear
Overall length	330 mm
Overall height	99 mm
Overall diameter	330 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Net Weight (Piece)	3.540 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Photobiological risk specification	18.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	35 °C
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	0.5

Stroboscopic effect visibility measure (SVM)	1
--	---

Ambient temperature range	-30 to +50 °C
---------------------------	---------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.316, 0.332) SDCM<5
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤5

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L85
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L75

Sustainability Data

Sustainability rating	Unclassified
Repair class	Repair Class D, this product is not designed to be repaired.
Embedded carbon (A1-A3)	62.3 kg CO ₂ e
Product non-virgin material ratio	6.64 %
Recyclable content ratio of the finished product	51.6 %
GWP total B6 (kg CO ₂ eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO ₂ eq / kwh)
GWP total B6 (kg CO ₂ eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) /lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO ₂ eq / kwh)

Product Data


Order product name	BY121P G5 LED200S/865 PSD WB
Full product name	BY121P G5 LED200S/865 PSD WB
Full product code	871951495581300
Order code	911401630708
Material Nr. (12NC)	911401630708
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514955813
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514955813

CoreLine Highbay Gen5

Dimensional drawing



Photometric data



Polar Normal (separate) - 911401630708

