



CoreLine Highbay Gen5

BY120P G5 LED150S/840 PSU NB

CoreLine Highbay Gen5, 88 W, 15000 lm, 4000 K, Narrow beam, IP65, IK08

CoreLine Highbay Gen5 delivers on the CoreLine promise of innovative, easy-to-use and high-quality luminaires. A reliable, highly-efficient luminaire with a very long-lifetime, it delivers great energy savings and requires less maintenance. At the same time, CoreLine Highbay is very easy to handle. The luminaire can be installed on your existing grid and the electrical connection is a straightforward task, with no need to open the luminaire and an external IP65 connector. With a choice of two beam angles: narrow and wide beam, you can adjust your lighting plan to suit your exact needs. This range also includes Interact Ready luminaires with integrated wireless communications and integrated movement and daylight sensors. So CoreLine Highbay Gen5 is ready to be used with any Interact connected lighting system.

Product data

General Information		Sustainability rating	
Light source replaceable	No	Unclassified	
Number of gear units	1 unit	Light Technical	
Driver included	Yes	Luminous Flux	15,000 lm
Service tag	Yes	Saturated Red (R9)	<50
Lighting Technology		Correlated Color Temperature (Nom)	4000 K
Value ladder	Performance	Luminous Efficacy (rated) (Nom)	170 lm/W
Serviceability class	Class C, luminaire without serviceable parts, not serviceable	Color rendering index (CRI)	>80
Warranty period	5 years	Light source color	840 neutral white
		Optic type	Narrow beam

CoreLine Highbay Gen5

Luminaire light beam spread	55°
Unified glare rating CEN	22

Sustainability Data

Embedded carbon (A1-A3)	46.1 kg CO _{2e}
Recyclable content ratio of the finished product	49.9 %
Product non-virgin material ratio	6.91 %
GWP total B6 (kg CO _{2eq}) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO _{2eq} / kwh)
GWP total B6 (kg CO _{2eq}) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) /lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO ₂ eq / kwh)

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	40 A
Inrush time	0.665 ms
Power Consumption	88 W
Power Factor (Fraction)	0.95
Connection	Connection unit 3-pole
Cable	Cable 0.3 m with connector 3-pole
Number of products on MCB of 16 A type B	6
Suitable for random switching	Yes
Protection class IEC	Safety class I
Total harmonic distortion	15 %

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Maximum dim level	Not applicable

Mechanical and Housing

Housing Material	Aluminum die-cast
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	Grey
Optical cover finish	Clear
Overall height	90 mm
Overall diameter	290 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

Mech. impact protection code	IK08 [5 J vandal-protected]
Net Weight (Piece)	1.990 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Photobiological risk specification	18.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	35 °C
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	0.5
Stroboscopic effect visibility measure (SVM)	1
Ambient temperature range	-30 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.385, 0.380) SDCM<5
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤5

Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L85
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L75

Product Data


Order product name	BY120P G5 LED150S/840 PSU NB
Full product name	BY120P G5 LED150S/840 PSU NB
Full product code	871951495596700
Order code	911401632208
Material Nr. (12NC)	911401632208
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514955967
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514955967

CoreLine Highbay Gen5

Dimensional drawing



Photometric data



Polar Normal (separate) - null - 911401632208

