



CoreLine Highbay Gen5

BY122P G5 LED300S/840 PSU WB

CoreLine Highbay Gen5, 181 W, 31000 lm, 4000 K, Wide beam, IP65, IK08

CoreLine Highbay Gen5 delivers on the CoreLine promise of innovative, easy-to-use and high-quality luminaires. A reliable, highly-efficient luminaire with a very long-lifetime, it delivers great energy savings and requires less maintenance. At the same time, CoreLine Highbay is very easy to handle. The luminaire can be installed on your existing grid and the electrical connection is a straightforward task, with no need to open the luminaire and an external IP65 connector. With a choice of two beam angles: narrow and wide beam, you can adjust your lighting plan to suit your exact needs. This range also includes Interact Ready luminaires with integrated wireless communications and integrated movement and daylight sensors. So CoreLine Highbay Gen5 is ready to be used with any Interact connected lighting system.

Product data

General Information		Sustainability rating	
Light source replaceable	No	Unclassified	
Number of gear units	1 unit	Light Technical	
Driver included	Yes	Luminous Flux	31,000 lm
Service tag	Yes	Saturated Red (R9)	<50
Lighting Technology	LED	Correlated Color Temperature (Nom)	4000 K
Value ladder	Performance	Luminous Efficacy (rated) (Nom)	171 lm/W
Serviceability class	Class C, luminaire without serviceable parts, not serviceable	Color rendering index (CRI)	>80
Warranty period	5 years	Light source color	840 neutral white
		Optic type	Wide beam

CoreLine Highbay Gen5

Luminaire light beam spread	85° x 85°
Unified glare rating CEN	25

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	54 A
Inrush time	0.75 ms
Power Consumption	181 W
Power Factor (Fraction)	0.95
Connection	Connection unit 3-pole
Cable	Cable 0.3 m with connector 3-pole
Number of products on MCB of 16 A type B	6
Suitable for random switching	Yes
Protection class IEC	Safety class I
Total harmonic distortion	15 %

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Maximum dim level	Not applicable

Mechanical and Housing

Housing Material	Aluminum die-cast
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	Grey
Optical cover finish	Clear
Overall height	99 mm
Overall diameter	393 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Net Weight (Piece)	4.190 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces

CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Photobiological risk specification	18.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	35 °C
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	0.5
Stroboscopic effect visibility measure (SVM)	1
Ambient temperature range	-30 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.385, 0.380) SDCM<5
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤5

Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L85
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L75

Product Data


Order product name	BY122P G5 LED300S/840 PSU WB
Full product name	BY122P G5 LED300S/840 PSU WB
Full product code	871951495601800
Order code	95601800
Material Nr. (12NC)	911401632708
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514956018
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514956018

CoreLine Highbay Gen5

Dimensional drawing



Photometric data



Polar Normal (separate) - null - 911401632708

