



# Tango G4 LED Flood

## BVP491 LED68/NW 50W SWB

Tango G4 LED Flood, 6800 lm, 50 W, White, depends on driver (1-10V, DALI...), Safety class I

Philips Tango G4 LED flood lighting is the 4th generation of the Tango LED family. A new range lighting that delivers higher efficacy and has an optimized windage area, and less weight thanks to its technical design. This product introduction is the ideal solution for a wide range of area lighting and recreational sports lighting applications. It incorporates the latest LED light source, one-piece optical system, heat sink and driver into a compact and robust housing that meets globally-recognized safety standards. Its specially-designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. Powered by LED technology, Tango G4 LED floodlights deliver superior performance and a longer lifetime, bringing area lighting to a whole new level.

### Warnings and Safety

- please pay attention to the mounting instructions

### Product data

General Information		Color rendering index (CRI)	
Driver included	Yes		>70
Service tag	Yes	Light source color	White
Lighting Technology	LED	Effective projected area	0.08 m <sup>2</sup>
Value ladder	Performance		
Light Technical		Operating and Electrical	
Luminous Flux	6,800 lm	Input Voltage	220-240 V
Correlated Color Temperature (Nom)	4000 K	Line Frequency	50 to 60 Hz
Luminous Efficacy (rated) (Nom)	140 lm/W	Inrush current	7.4 A
		Power Consumption	50 W
		Power Factor (Fraction)	0.95

# Tango G4 LED Flood

Connection	Flying leads/wires
Cable	Cable 0.5 m without plug
Number of products on MCB of 16 A type B 24	
Protection class IEC	Safety class I
<b>Controls and Dimming</b>	
Dimmable	No
Control interface	depends on driver (1-10V, DALI...)
<b>Mechanical and Housing</b>	
Housing Material	Aluminum Alloy
Optical cover material	Polycarbonate
Housing Color	Gray
Overall length	266 mm
Overall width	386 mm
Overall height	84 mm
Dimensions (Height x Width x Depth)	84 x 386 x 266 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Glass
Net Weight (Piece)	5.000 kg
<b>Approval and Application</b>	
Flammability mark	For mounting on normally flammable surfaces

CE mark	Yes
Ambient temperature range	-40 to +50 °C
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Initial chromaticity	7
Power consumption tolerance	+/-10%
<b>Product Data</b>	
Order product name	BVP491 LED68/NW 50W SWB
Full product name	BVP491 LED68/NW 50W SWB
Full product code	692234197814200
Order code	911401658207
Material Nr. (12NC)	911401658207
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6922341978142
Numerator - Packs per outer box	1
EAN/UPC - Case	6922341978142

## Dimensional drawing

