



Tango Pro

BVP561 LED187/740 120W WLP AMB

Tango Pro, 18714 lm, 120 W, 740 neutral white, 89°, depends on driver (1-10V, DALI...), Safety class I, Mounting bracket

Philips Tango Pro LED floodlight is the fifth generation of the Philips Tango LED floodlight. Tango Pro takes efficiency to the next level, delivering industry-best efficiency in a compact but elegant design. The luminaire can be applied in a versatile range of applications, from area lighting to recreational sports facilities. The LED driver comes in compact and robust housing that meets globally recognized safety standards. Its specially designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. The modular, streamlined luminaire silhouette offers a visually balanced design. Philips Tango Pro LED floodlight is engineered to create brighter and safer environments. Powered by the latest LED technology, Tango Pro delivers superior performance in both light distribution and UltraEfficiency 170lm/W and up to 200lm/W. The long luminaire lifetime and recyclable materials supports your efforts to meet sustainability targets.

Warnings and Safety

- For coastline applications, 2,000 hours (or above) MSP recommended (liability for wear-and-tear damages exempted)
- Not suitable for chemical industrial areas
- Not suitable for installation on moving objects

Product data

General Information		Luminous Efficacy (rated) (Nom)	156 lm/W
Driver included	Yes	Color rendering index (CRI)	70
Value ladder	Performance	Light source color	740 neutral white
Light Technical		Optic type	Assymetric Beam angle
Luminous Flux	18,714 lm	Luminaire light beam spread	89°
Correlated Color Temperature (Nom)	4000 K	Effective projected area	0.078 m ²

Tango Pro

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Inrush current	45 A
Inrush time	0.315 ms
Power Consumption	120 W
Power Factor (Fraction)	0.9
Connection	Flying leads/wires
Cable	-
Protection class IEC	Safety class I

Controls and Dimming

Dimmable	1-10V
Control interface	depends on driver (1-10V, DALI...)

Mechanical and Housing

Housing Material	Aluminium die-cast ADC1 - alloy grade (EN AC-47100)
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	RAL7040
Mounting device	Mounting bracket
Optical cover finish	Diffused lens optic
Overall length	315 mm
Overall width	349 mm

Overall height	82 mm
Dimensions (Height x Width x Depth)	82 x 349 x 315 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [6 J]
Optical cover type	Polycarbonate
Net Weight (Piece)	4.450 kg

Approval and Application

Flammability mark	-
CE mark	Yes
Ambient temperature range	-40 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BVP561 LED187/740 120W WLP AMB
Full product name	BVP561 LED187/740 120W WLP AMB
Order code	911401663009
Material Nr. (12NC)	911401663009
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

