



Tango G4 LED Flood

BVP493 LED341/NW 255W SWB

Tango G4 LED Flood, 34100 lm, 255 W, White, depends on driver (1-10V, DALI...), Safety class I

Philips Tango G4 LED flood lighting is the 4th generation of the Tango LED family. A new range lighting that delivers higher efficacy and has an optimized windage area, and less weight thanks to its technical design. This product introduction is the ideal solution for a wide range of area lighting and recreational sports lighting applications. It incorporates the latest LED light source, one-piece optical system, heat sink and driver into a compact and robust housing that meets globally-recognized safety standards. Its specially-designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. Powered by LED technology, Tango G4 LED floodlights deliver superior performance and a longer lifetime, bringing area lighting to a whole new level.

Warnings and Safety

- please pay attention to the mounting instructions

Product data

General Information		Color rendering index (CRI)	
Driver included	Yes		>70
Service tag	Yes	Light source color	White
Lighting Technology	LED	Effective projected area	0.25 m ²
Value ladder	Performance		
Light Technical		Operating and Electrical	
Luminous Flux	34,100 lm	Input Voltage	220-240 V
Correlated Color Temperature (Nom)	4000 K	Line Frequency	50 to 60 Hz
Luminous Efficacy (rated) (Nom)	140 lm/W	Inrush current	92 A
		Power Consumption	255 W
		Power Factor (Fraction)	0.95

Tango G4 LED Flood

Connection	Flying leads/wires
Cable	Cable 0.5 m without plug
Number of products on MCB of 16 A type B 5	
Protection class IEC	Safety class I
Controls and Dimming	
Dimmable	No
Control interface	depends on driver (1-10V, DALI...)
Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Polycarbonate
Housing Color	Gray
Overall length	523 mm
Overall width	525 mm
Overall height	113 mm
Dimensions (Height x Width x Depth)	113 x 525 x 523 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Glass
Net Weight (Piece)	13.480 kg
Approval and Application	
Flammability mark	For mounting on normally flammable surfaces

CE mark	Yes
Ambient temperature range	-40 to +50 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	7
Power consumption tolerance	+/-10%
Product Data	
Order product name	BVP493 LED341/NW 255W SWB
Full product name	BVP493 LED341/NW 255W SWB
Full product code	692234197884500
Order code	97884500
Material Nr. (12NC)	911401665207
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6922341978845
Numerator - Packs per outer box	1
EAN/UPC - Case	6922341978845

Dimensional drawing

