



GreenVision All-in-one Solar Street Light

BRP715 LED70 WW Solar Pro

Integrated solar street light with Lithium Ferro Phosphate battery, solar panel and MPPT charge controller built into the luminaire. Pressure die cast aluminium for sturdiness and long life. Specially designed pole mounting bracket allows different tilt angles, lateral and pole top mounting. Adjustable LED module for better distribution of light when required.

Product data

General Information		Controls and Dimming	
Driver included	Yes	Dimmable	Yes
Light Technical		Configurability	Configurable
Luminous Flux	7,200 lm	Solar dimming profile	Dimming along with microwave motion sensor
Correlated Color Temperature (Nom)	5700 K	Mechanical and Housing	
Color rendering index (CRI)	>70	Housing Color	Black
Operating and Electrical		Overall length	1,345 mm
Battery type	LiFePO4	Overall width	366 mm
Battery ampere hour	42 Ah	Overall height	133 mm
Battery voltage	12.8 V	Dimensions (Height x Width x Depth)	133 x 366 x 1345 mm
Battery charging & discharging cycles	2000	Material	Aluminum
Panel type	Mono crystalline	Battery location	Inbuilt
Panel voltage	18 V	Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Panel peak wattage	80 W	Mech. impact protection code	IK08 [5 J vandal-protected]
Charge controller type	MPPT	Optical cover type	Polycarbonate bowl/cover
Cable	-	Net Weight (Piece)	15.340 kg
Grid connection type	Off grid	Approval and Application	
		CE mark	Yes

GreenVision All-in-one Solar Street Light

Ambient temperature range	-10 °C to 55 °C
Product Data	
Order product name	BRP715 LED70 WW Solar Pro
Full product name	BRP715 LED70 WW Solar Pro
Full product code	872016950730200
Order code	911401668908

Material Nr. (12NC)	911401668908
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169507302
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169507302

Dimensional drawing

