PHILIPS

Lighting

# GreenVision All-in-one Solar Street Light

## BRP715 LED90 WW Solar 5

Integrated solar street light with Lithium Ferro Phosphate battery, solar panel and MPPT charge controller built into the luminaire. Pressure die cast aluminium for sturdiness and long life. Specially designed pole mounting bracket allows different tilt angles, lateral and pole top mounting. Adjustable LED module for better distribution of light when required.

### Product data

| General Information | |
|---|---|
| **Driver included** | Yes |

| Light Technical | |
|---|---|
| **Luminous Flux** | 9,000 lm |
| **Correlated Color Temperature (Nom)** | 5700 K |
| **Color rendering index (CRI)** | >70 |

| Operating and Electrical | |
|---|---|
| **Battery type** | LiFePO4 |
| **Battery ampere hour** | 24 Ah |
| **Battery voltage** | 12.8 V |
| **Battery charging & discharging cycles** | 2000 |
| **Panel type** | Mono crystalline |
| **Panel voltage** | 18 V |
| **Panel peak wattage** | 50 W |
| **Charge controller type** | MPPT |
| **Cable** | - |
| **Grid connection type** | Off grid |

| Controls and Dimming | |
|---|---|
| **Dimmable** | Yes |
| **Configurability** | Configurable |
| **Solar dimming profile** | Dimming along with mircowave motion sensor |

| Mechanical and Housing | |
|---|---|
| **Housing Color** | Black |
| **Overall length** | 910 mm |
| **Overall width** | 366 mm |
| **Overall height** | 133 mm |
| **Dimensions (Height x Width x Depth)** | 133 x 366 x 910 mm |
| **Material** | Aluminum |
| **Battery location** | Inbuilt |
| **Ingress protection code** | IP65 [Dust penetration-protected, jet-proof] |
| **Mech. impact protection code** | IK08 [5 J vandal-protected] |
| **Optical cover type** | Polycarbonate bowl/cover |
| **Net Weight (Piece)** | 11.840 kg |

| Approval and Application | |
|---|---|
| **CE mark** | Yes |

# GreenVision All-in-one Solar Street Light

| | |
|---|---|
| **Ambient temperature range** | -10 °C to 55 °C |

## Product Data

| | |
|---|---|
| **Order product name** | BRP715 LED90 WW Solar 5 |
| **Full product name** | BRP715 LED90 WW Solar 5 |
| **Full product code** | 872016950736400 |
| **Order code** | 911401669508 |

| | |
|---|---|
| **Material Nr. (12NC)** | 911401669508 |
| **Numerator - Quantity Per Pack** | 1 |
| **EAN/UPC - Product/Case** | 8720169507364 |
| **Numerator - Packs per outer box** | 1 |
| **EAN/UPC - Case** | 8720169507364 |

## Dimensional drawing



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.