



**BRP582 LED222/NW
150W DM GL**

911401688109



GreenVision Xceed Pro, 22200 lm, 150 W, White, depends on driver (1-10V, DALI...), Safety class I

Engineered for excellence, Xceed Pro has been upgraded to reduce costs while enhancing efficiency, safety, and functionality. Its refined design seamlessly blends a clean and attractive aesthetic with superior performance, ensuring it complements modern streetscapes. Beyond its visual appeal, Xceed Pro delivers cutting-edge capabilities: future-proof technology, industry-leading efficacy, world-class lighting design, effortless maintenance, flexible installation, smart connectivity. Furthermore, the range thoughtfully addresses environmentally sensitive road and street lighting needs by offering options with low blue spectrum color temperatures, ensuring harmony with both urban and natural surroundings.

General Information

| | |
|-----------------|---------------|
| Driver included | Yes |
| Value ladder | Specification |

Light Technical

| | |
|------------------------------------|-----------|
| Luminous Flux | 22,200 lm |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (rated) (Nom) | 148 lm/W |
| Color rendering index (CRI) | 70 |
| Light source color | White |

Operating and Electrical

| | |
|-------------------------|-------------------------------|
| Input Voltage | 220-240 V |
| Line Frequency | 50 or 60 Hz |
| Inrush current | 55 A |
| Power Consumption | 150 W |
| Power Factor (Fraction) | 0.95 |
| Connection | Screw connection block 3-pole |
| Cable | - |
| Protection class IEC | Safety class I |

Controls and Dimming

| | |
|-------------------|------------------------------------|
| Dimmable | Yes |
| Control interface | depends on driver (1-10V, DALI...) |

Mechanical and Housing

| | |
|-------------------------------------|--------------------|
| Housing Material | Aluminium |
| Reflector material | Polycarbonate |
| Optical cover material | Tempered glass |
| Housing Color | RAL7040 |
| Overall length | 506 mm |
| Overall width | 309 mm |
| Overall height | 120 mm |
| Dimensions (Height x Width x Depth) | 120 x 309 x 506 mm |

| | |
|------------------------------|--|
| Ingress protection code | IP66 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK09 [10 J] |
| Optical cover type | Tempered glass |
| Net Weight (Piece) | 4.200 kg |

Approval and Application

| | |
|------------------------------------|---------------|
| CE mark | Yes |
| Performance ambient temperature Tq | 35 °C |
| Ambient temperature range | -40 to +50 °C |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|-------------|
| Luminous flux tolerance | -10% / +10% |
| Power consumption tolerance | +/-10% |


Product Data

| | |
|---------------------------------|-----------------------------|
| Order product name | BRP582 LED222/NW 150W DM GL |
| Full product name | BRP582 LED222/NW 150W DM GL |
| Order code | 911401688109 |
| Material Nr. (12NC) | 911401688109 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |

Dimensional drawing

BRP582

Side Entry



Post Top

