



**BRP582 LED167/NW 100W  
DM PSRD**

911401689809



## GreenVision Xceed Pro, 16700 lm, 100 W, White, depends on driver (1-10V, DALI...), Safety class I

Engineered for excellence, Xceed Pro has been upgraded to reduce costs while enhancing efficiency, safety, and functionality. Its refined design seamlessly blends a clean and attractive aesthetic with superior performance, ensuring it complements modern streetscapes. Beyond its visual appeal, Xceed Pro delivers cutting-edge capabilities: future-proof technology, industry-leading efficacy, world-class lighting design, effortless maintenance, flexible installation, smart connectivity. Furthermore, the range thoughtfully addresses environmentally sensitive road and street lighting needs by offering options with low blue spectrum color temperatures, ensuring harmony with both urban and natural surroundings.

### General Information

Driver included	Yes
Value ladder	Specification

### Light Technical

Luminous Flux	16,700 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	167 lm/W
Color rendering index (CRI)	70
Light source color	White

## Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Inrush current	76.5 A
Power Consumption	100 W
Power Factor (Fraction)	0.95
Connection	Screw connection block 3-pole
Cable	-
Protection class IEC	Safety class I

## Controls and Dimming

Dimmable	Yes
Control interface	depends on driver (1-10V, DALI...)

## Mechanical and Housing

Housing Material	Aluminium
Reflector material	Polycarbonate
Optical cover material	Tempered glass
Housing Color	RAL7040
Overall length	506 mm
Overall width	309 mm
Overall height	120 mm
Dimensions (Height x Width x Depth)	120 x 309 x 506 mm

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Optical cover type	Tempered glass
Net Weight (Piece)	4.200 kg

## Approval and Application

CE mark	Yes
Performance ambient temperature Tq	50 °C
Ambient temperature range	-40 to +50 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%


## Product Data

Order product name	BRP582 LED167/NW 100W DM PSRD
Full product name	BRP582 LED167/NW 100W DM PSRD
Order code	911401689809
Material Nr. (12NC)	911401689809
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Dimensional drawing

BRP582

Side Entry



Post Top

