



Uni Wall Sconce

BWP410 LED WW 220V 40W WB PSU 7012

Uni Wall Sconce, 5000 lm, 40 W, 730 warm white, Safety class I

Public areas all seek for the most reliable and professional lighting solutions, e.g., parking areas, entrances, outdoor terrace, and wall in garden. The Philips Uni Wall Mount Sconce can be installed easily in accordance with per scenario, delivering the optimized lighting to surroundings. The modern sleek design makes the fixture suitable to be installed either in renovation or new installation scenarios. The Philips Uni Wall Mount sconce helps you achieve superb reliability and more. Same as other product range in Philips, the product is designed under a variety of Philips quality standard with a good price/quality ratio. Therefore, Philips Uni Wall Mount Sconce offers another affordable, energy – efficient and stable choice in the existing wall Mounting family.

Product data

| General Information | | Line Frequency | |
|------------------------------------|----------------|-------------------------|------------------------|
| Driver included | Yes | Line Frequency | 50 or 60 Hz |
| Light source engine type | LED | Power Consumption | 40 W |
| Value ladder | Performance | Power Factor (Fraction) | 0.95 |
| Warranty period | 3 years | Connection | Connection unit 3-pole |
| Light Technical | | Cable | Cable without plug |
| Luminous Flux | 5,000 lm | Protection class IEC | Safety class I |
| Correlated Color Temperature (Nom) | 3000 K | Controls and Dimming | |
| Luminous Efficacy (rated) (Nom) | 125 lm/W | Dimmable | No |
| Color rendering index (CRI) | 70 | Control interface | - |
| Light source color | 730 warm white | Mechanical and Housing | |
| Operating and Electrical | | Housing Material | Aluminum die-cast |
| Input Voltage | 220 to 240 V | Optical cover material | Tempered glass |
| | | Housing Color | Gray |

Uni Wall Sconce

| | |
|-------------------------------------|--|
| Overall length | 222 mm |
| Overall width | 150 mm |
| Overall height | 359 mm |
| Dimensions (Height x Width x Depth) | 359 x 150 x 222 mm |
| Ingress protection code | IP65 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK08 [5 J vandal-protected] |
| Optical cover type | Flat glass |
| Net Weight (Piece) | 4.190 kg |

Approval and Application

| | |
|---------------------------|---------------|
| CE mark | Yes |
| Ambient temperature range | -40 to +50 °C |

Initial Performance (IEC Compliant)

| | |
|-------------------------|--------|
| Luminous flux tolerance | +/-10% |
|-------------------------|--------|

| | |
|-----------------------------|--------|
| Power consumption tolerance | +/-10% |
|-----------------------------|--------|

Product Data

| | |
|---------------------------------|------------------------------------|
| Order product name | BWP410 LED WW 220V 40W WB PSU 7012 |
| Full product name | BWP410 LED WW 220V 40W WB PSU 7012 |
| Full product code | 692382861084599 |
| Order code | 61084599 |
| Material Nr. (12NC) | 911401696908 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 6923828610845 |
| Numerator - Packs per outer box | 4 |
| EAN/UPC - Case | 6923828611118 |

Dimensional drawing

