



# Uni Wall Mount Recessed

## BWP400 LED WW 220V 12W WB PSU 7012

Uni Wall Mount Recessed, 580 lm, 12 W, 730 warm white, Safety class I

Public areas all seek for the most reliable and professional lighting solutions, e.g. parking areas, entrances, outdoor terrace and wall in garden. The Philips Uni Wall Mount Recessed can be installed easily in accordance with each scenario, delivering the optimised lighting to surroundings. The modern sleek design makes the fixture suitable to be installed either in renovation or new installation scenarios. The Philips Uni Wall Mount Recessed helps you achieve superb reliability and more. Same as other product range in Philips, the product is designed under a variety of Philips quality standard with a good price/quality ratio. Therefore, Philips Uni Wall Mount Recessed offers another affordable, energy-efficient and stable choice in wall mounting family.

### Product data

General Information		Light source colour	
Driver included	Yes	730 warm white	
Light source engine type	LED	Operating and Electrical	
Value ladder	Performance	Input Voltage	220 to 240 V
Warranty period	3 years	Line Frequency	50 or 60 Hz
Light Technical		Power Consumption	12 W
Luminous Flux	580 lm	Power Factor (Fraction)	0.9
Correlated Colour Temperature (Nom)	3000 K	Connection	Connection unit 3-pole
Luminous efficacy (rated) (nom.)	48 lm/W	Cable	Cable without plug
Colour rendering index (CRI)	70	Protection class IEC	Safety class I

# Uni Wall Mount Recessed

## Controls and Dimming

Dimmable	No
Control interface	-

## Mechanical and Housing

Housing material	Aluminium die-cast
Optical cover/lens material	Tempered glass
Housing Colour	Grey
Overall length	205 mm
Overall width	107 mm
Overall height	71 mm
Dimensions (height x width x depth)	71 x 107 x 205 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Flat glass
Net Weight (Piece)	0.890 kg

## Approval and Application

CE mark	Yes
---------	-----

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

## Product Data

Order product name	BWP400 LED WW 220V 12W WB PSU 7012
Full product name	BWP400 LED WW 220V 12W WB PSU 7012
Full EOC	692382861102699
Order code	911401698508
Material no. (12 NC)	911401698508
Numerator – quantity per pack	1
EAN/UPC – Product/Case	6923828611026
Numerator – packs per outer box	12
EAN/UPC – Case	6923828611286

## Dimensional drawing

