



UniPoint

BGP312 1LED 3000K NB

UniPoint, 120 lm, 3 W, 830 warm white, Narrow beam angle 10°, 10°, Safety class III, Allen screw fixation

Our UniPoint is designed to produce both general and accent lighting while concealing the body of the device, allowing only the light to be exposed. This design can be used to change the surroundings by adding subtle or dramatic contrasting effects. It also includes exclusive features such as energy efficiency, chromatic quality and miniaturization. We guarantee extreme reliability and high level of resistance to adverse weather conditions and vandalism

Product data

General Information	
Light source replaceable	No
Driver included	No
Light source engine type	LED
Lighting Technology	LED
Value ladder	Performance
Warranty period	3 years
Light Technical	
Luminous Flux	120 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	40 lm/W
Color rendering index (CRI)	>75
Light source color	830 warm white
Luminaire light beam spread	10°
Optic type outdoor	Narrow beam angle 10°

Operating and Electrical	
Input Voltage	24 DC V
Line Frequency	45 to 66 Hz
Inrush current	0.5 A
Inrush time	10 ms
Power Consumption	3 W
Power Factor (Fraction)	0.97
Connection	Flying leads/wires
Cable	Cable without plug 2-pole
Protection class IEC	Safety class III
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Electronic transformer
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Glass
Optical cover material	Glass
Housing Color	Dark gray
Mounting device	Allen screw fixation
Optical cover shape	Conical
Optical cover finish	Textured
Overall length	95.8 mm
Overall height	69.4 mm
Overall diameter	65.5 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Optical cover type	Glass bowl/cover
Net Weight (Piece)	0.400 kg

Approval and Application

CE mark	No
---------	----

EU RoHS compliant	Yes
Ambient temperature range	-20 to +45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<5
Power consumption tolerance	+/-10%

Product Data

Order product name	BGP312 1LED 3000K NB
Full product name	BGP312 1LED 3000K NB
Full product code	911401710672
Order code	911401710672
Material Nr. (12NC)	911401710672
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	32

Dimensional drawing

