



# GreenSpace Flex

## RS378B MR16 D78 S-S AJ D

Accessory, GreenSpace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

### Product data

| General Information      |             |
|--------------------------|-------------|
| Number of gear units     | 1 unit      |
| Driver included          | No          |
| Light source engine type | -           |
| Value ladder             | Performance |
| Warranty period          | 3 years     |

| Light Technical                    |             |
|------------------------------------|-------------|
| Correlated Color Temperature (Nom) | -           |
| Color rendering index (CRI)        | >90         |
| Beam angle of light source         | - degree(s) |
| Light source color                 | -           |
| Optic type                         | -           |
| Luminaire light beam spread        | -           |

| Operating and Electrical |                    |
|--------------------------|--------------------|
| Input Voltage            | 220 to 240 V       |
| Line Frequency           | 50 or 60 Hz        |
| Power Consumption        | 10 W               |
| Power Factor (Fraction)  | 0.9                |
| Connection               | External connector |

|  |                 |
|--|-----------------|
| Cable                                    | -               |
| Number of products on MCB of 16 A type B | -               |
| Suitable for random switching            | No              |
| Protection class IEC                     | Safety class II |

| Controls and Dimming          |                        |
|-------------------------------|------------------------|
| Dimmable                      | No                     |
| Driver/power unit/transformer | Electronic transformer |
| Control interface             | -                      |
| Constant light output         | No                     |
| Maximum dim level             | Not applicable         |

| Mechanical and Housing |                         |
|------------------------|-------------------------|
| Housing Material       | Aluminum Alloy          |
| Reflector material     | -                       |
| Optic material         | Polymethyl methacrylate |
| Optical cover material | -                       |
| Fixation material      | Aluminum                |
| Housing Color          | Dark gray               |
| Optical cover finish   | -                       |
| Overall length         | 85 mm                   |

## Greenspace Flex

|                                     |                            |
|-------------------------------------|----------------------------|
| Overall width                       | 85 mm                      |
| Overall height                      | 103 mm                     |
| Overall diameter                    | 0 mm                       |
| Dimensions (Height x Width x Depth) | 103 x 85 x 85 mm           |
| Material                            | Aluminum                   |
| Ingress protection code             | IP20 [Finger-protected]    |
| Mech. impact protection code        | IK04 [0.5 J standard plus] |
| Accessory color                     | Dark gray                  |
| Optical cover type                  | -                          |
| Net Weight (Piece)                  | 0.150 kg                   |

### Approval and Application

|                           |                                   |
|---------------------------|-----------------------------------|
| Glow-wire test            | Temperature 600 °C, duration 30 s |
| Flammability mark         | -                                 |
| CE mark                   | No                                |
| ENEC mark                 | -                                 |
| EU RoHS compliant         | Yes                               |
| Ambient temperature range | -20 to +45 °C                     |

### Initial Performance (IEC Compliant)

|                             |        |
|-----------------------------|--------|
| Luminous flux tolerance     | +/-10% |
| Power consumption tolerance | +/-10% |

### Over Time Performance (IEC Compliant)

|                           |                |
|---------------------------|----------------|
| Median useful life L80B50 | 50,000 hour(s) |
|---------------------------|----------------|

### Product Data

|                                 |                          |
|---------------------------------|--------------------------|
| Order product name              | RS378B MR16 D78 S-S AJ D |
| Full product name               | RS378B MR16 D78 S-S AJ D |
| Full product code               | 911401720842             |
| Order code                      | 911401720842             |
| Material Nr. (12NC)             | 911401720842             |
| Numerator - Quantity Per Pack   | 1                        |
| Numerator - Packs per outer box | 36                       |

## Dimensional drawing

