



Greenspace Flex

RS378B MR16 D92 R-R FX D

Accessory, Greenspace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Product data

| General Information | |
|--------------------------|-------------|
| Number of gear units | 1 unit |
| Driver included | No |
| Light source engine type | - |
| Value ladder | Performance |
| Warranty period | 3 years |

| Light Technical | |
|------------------------------------|-------------|
| Correlated Color Temperature (Nom) | - |
| Color rendering index (CRI) | >90 |
| Beam angle of light source | - degree(s) |
| Light source color | - |
| Optic type | - |
| Luminaire light beam spread | - |

| Operating and Electrical | |
|--------------------------|--------------------|
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 or 60 Hz |
| Power Consumption | 10 W |
| Power Factor (Fraction) | 0.9 |
| Connection | External connector |

| | |
|--|-----------------|
| Cable | - |
| Number of products on MCB of 16 A type B | - |
| Suitable for random switching | No |
| Protection class IEC | Safety class II |

| Controls and Dimming | |
|-------------------------------|------------------------|
| Dimmable | No |
| Driver/power unit/transformer | Electronic transformer |
| Control interface | - |
| Constant light output | No |
| Maximum dim level | Not applicable |

| Mechanical and Housing | |
|------------------------|-------------------------|
| Housing Material | Aluminum Alloy |
| Reflector material | - |
| Optic material | Polymethyl methacrylate |
| Optical cover material | - |
| Fixation material | Aluminum |
| Housing Color | Dark gray |
| Optical cover finish | - |
| Overall length | 0 mm |

Greenspace Flex

| | |
|-------------------------------------|----------------------------|
| Overall width | 0 mm |
| Overall height | 110 mm |
| Overall diameter | 105 mm |
| Dimensions (Height x Width x Depth) | 110 x 0 x 0 mm |
| Material | Aluminum |
| Ingress protection code | IP20 [Finger-protected] |
| Mech. impact protection code | IK04 [0.5 J standard plus] |
| Accessory color | Dark gray |
| Optical cover type | - |
| Net Weight (Piece) | 0.210 kg |

Approval and Application

| | |
|---------------------------|-----------------------------------|
| Glow-wire test | Temperature 600 °C, duration 30 s |
| Flammability mark | - |
| CE mark | No |
| ENEC mark | - |
| EU RoHS compliant | Yes |
| Ambient temperature range | -20 to +45 °C |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|--------|
| Luminous flux tolerance | +/-10% |
| Power consumption tolerance | +/-10% |

Over Time Performance (IEC Compliant)

| | |
|---------------------------|----------------|
| Median useful life L80B50 | 50,000 hour(s) |
|---------------------------|----------------|

Product Data

| | |
|---------------------------------|--------------------------|
| Order product name | RS378B MR16 D92 R-R FX D |
| Full product name | RS378B MR16 D92 R-R FX D |
| Full product code | 911401720862 |
| Order code | 911401720862 |
| Material Nr. (12NC) | 911401720862 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 36 |

Dimensional drawing

