



# Greenspace Flex

## RS378B MR16 D102 R-R FX D

Accessory, Greenspace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

### Product data

General Information	
Number of gear units	1 unit
Driver included	No
Light source engine type	-
Value ladder	Performance
Warranty period	3 years

Light Technical	
Correlated Color Temperature (Nom)	-
Color rendering index (CRI)	>90
Beam angle of light source	- degree(s)
Light source color	-
Optic type	-
Luminaire light beam spread	-

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	10 W
Power Factor (Fraction)	0.9
Connection	External connector

Cable	-
Number of products on MCB of 16 A type B	-
Suitable for random switching	No
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Electronic transformer
Control interface	-
Constant light output	No
Maximum dim level	Not applicable

Mechanical and Housing	
Housing Material	Aluminum Alloy
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	-
Fixation material	Aluminum
Housing Color	Dark gray
Optical cover finish	-
Overall length	0 mm

## Greenspace Flex

Overall width	0 mm
Overall height	114 mm
Overall diameter	115 mm
Dimensions (Height x Width x Depth)	114 x 0 x 0 mm
Material	Aluminum
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]
Accessory color	Dark gray
Optical cover type	-
Net Weight (Piece)	0.250 kg

### Approval and Application

Glow-wire test	Temperature 600 °C, duration 30 s
Flammability mark	-
CE mark	No
ENEC mark	-
EU RoHS compliant	Yes
Ambient temperature range	-20 to +45 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%


### Over Time Performance (IEC Compliant)

Median useful life L80B50	50,000 hour(s)
---------------------------	----------------

### Product Data

Order product name	RS378B MR16 D102 R-R FX D
Full product name	RS378B MR16 D102 R-R FX D
Full product code	911401720882
Order code	911401720882
Material Nr. (12NC)	911401720882
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24

## Dimensional drawing



Cut out: Ø92

