



UniSpot

BVP378 4LED 40K 220V 20 RDM 50W COB

UniSpot, 3925 lm, 50 W, 840 neutral white, DMX, Safety class I

Philips UniSpot features a sophisticated and compact design that balances beauty and functionality, unobtrusively blending into diverse urban applications. Spotlights in the UniSpot range feature a cylindrical geometry separated into two sections. The front section provides illumination, while the back section connects to heating or other systems using a variety of accessories. Two indication plates on the stand and base make the installation process simple and easy.

Product data

General Information		Protection class IEC	
Driver included	Yes	Protection class IEC	Safety class I
Light Technical		Controls and Dimming	
Luminous Flux	3,925 lm	Dimmable	Yes
Correlated Color Temperature (Nom)	4000 K	Control interface	DMX
Luminous Efficacy (rated) (Nom)	78 lm/W	Mechanical and Housing	
Color rendering index (CRI)	>80	Housing Material	Aluminum Alloy
Light source color	840 neutral white	Optical cover material	Glass
Operating and Electrical		Housing Color	Dark gray
Input Voltage	220 to 240 V	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Line Frequency	50 or 60 Hz	Mech. impact protection code	IK06 [1 J]
Power Consumption	50 W	Optical cover type	Clear glass
Power Factor (Fraction)	0.9	Net Weight (Piece)	2.850 kg
Connection	Flying leads/wires and 2 Push-in connector 4-pole	Approval and Application	
Cable	Cable 0.3 m without plug 3-pole + 2 Cables 0.3 m with connector 4-pole	CE mark	Yes
		Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BVP378 4LED 40K 220V 20 RDM 50W COB
Full product name	BVP378 4LED 40K 220V 20 RDM 50W COB
Full product code	87211037029999

Order code	911401733534
Material Nr. (12NC)	911401733534
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103702999
Numerator - Packs per outer box	6
EAN/UPC - Case	8721103702999

Dimensional drawing

