



UniSpot

BVP378 4LED RGB 220V 10 RDM 50W

UniSpot, 1155 lm, 50 W, Red, green and blue, DMX, Safety class I

Philips UniSpot features a sophisticated and compact design that balances beauty and functionality, unobtrusively blending into diverse urban applications. Spotlights in the UniSpot range feature a cylindrical geometry separated into two sections. The front section provides illumination, while the back section connects to heating or other systems using a variety of accessories. Two indication plates on the stand and base make the installation process simple and easy.

Product data

General Information		Protection class IEC	Safety class I
Driver included	Yes	Controls and Dimming	
Light Technical		Dimmable	Yes
Luminous Flux	1,155 lm	Control interface	DMX
Correlated Color Temperature (Nom) -		Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	23 lm/W	Housing Material	Aluminum Alloy
Color rendering index (CRI)	>80	Optical cover material	Glass
Light source color	Red, green and blue	Housing Color	Dark gray
Operating and Electrical		Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Input Voltage	220 to 240 V	Mech. impact protection code	IK06 [1 J]
Line Frequency	50 or 60 Hz	Optical cover type	Clear glass
Power Consumption	50 W	Net Weight (Piece)	2.850 kg
Power Factor (Fraction)	0.9	Approval and Application	
Connection	Flying leads/wires and 2 Push-in connector 4-pole	CE mark	Yes
Cable	Cable 0.3 m without plug 3-pole + 2 Cables 0.3 m with connector 4-pole	Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	BVP378 4LED RGB 220V 10 RDM 50W
Full product name	BVP378 4LED RGB 220V 10 RDM 50W
Full product code	872110370306499

Order code	911401733604
Material Nr. (12NC)	911401733604
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103703064
Numerator - Packs per outer box	6
EAN/UPC - Case	8721103703064

Dimensional drawing

