



UniSpot

BVP378 4LED RGB40K 220V 15 RDM 50W

UniSpot, 1600 lm, 50 W, Red, green, blue and white, DMX, Safety class I

Philips UniSpot features a sophisticated and compact design that balances beauty and functionality, unobtrusively blending into diverse urban applications. Spotlights in the UniSpot range feature a cylindrical geometry separated into two sections. The front section provides illumination, while the back section connects to heating or other systems using a variety of accessories. Two indication plates on the stand and base make the installation process simple and easy.

Product data

General Information	
Driver included	Yes
Light Technical	
Luminous Flux	1,600 lm
Correlated Color Temperature (Nom)	RGBW
Luminous Efficacy (rated) (Nom)	32 lm/W
Color rendering index (CRI)	>80
Light source color	Red, green, blue and white
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	50 W
Power Factor (Fraction)	0.9
Connection	Flying leads/wires and 2 Push-in connector 4-pole

Cable	Cable 0.3 m without plug 3-pole + 2 Cables 0.3 m with connector 4-pole
Protection class IEC	Safety class I
Controls and Dimming	
Dimmable	Yes
Control interface	DMX
Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Glass
Housing Color	Dark gray
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Clear glass
Net Weight (Piece)	2.850 kg

Approval and Application

CE mark	Yes
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BVP378 4LED RGB40K 220V 15 RDM 50W
--------------------	------------------------------------

Full product name	BVP378 4LED RGB40K 220V 15 RDM 50W
Full product code	872110370308899
Order code	911401733624
Material Nr. (12NC)	911401733624
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103703088
Numerator - Packs per outer box	6
EAN/UPC - Case	8721103703088

Dimensional drawing

