



UniSpot

BVP375 1LED 30K 24V 35 10W COB

UniSpot, 890 lm, 10 W, 830 warm white, Safety class III

Philips UniSpot features a sophisticated and compact design that balances beauty and functionality, unobtrusively blending into diverse urban applications. Spotlights in the UniSpot range feature a cylindrical geometry separated into two sections. The front section provides illumination, while the back section connects to heating or other systems using a variety of accessories. Two indication plates on the stand and base make the installation process simple and easy.

Product data

General Information		Controls and Dimming	
Driver included	No	Dimmable	No
		Control interface	-
Light Technical		Mechanical and Housing	
Luminous Flux	890 lm	Housing Material	Aluminum Alloy
Correlated Color Temperature (Nom)	3000 K	Optical cover material	Glass
Luminous Efficacy (rated) (Nom)	89 lm/W	Housing Color	Dark gray
Color rendering index (CRI)	>80	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Light source color	830 warm white	Mech. impact protection code	IK06 [1 J]
		Optical cover type	Clear glass
		Net Weight (Piece)	0.500 kg
Operating and Electrical		Approval and Application	
Input Voltage	24 V	CE mark	Yes
Line Frequency	- Hz	Ambient temperature range	-40 to +50 °C
Power Consumption	10 W		
Power Factor (Fraction)	-		
Connection	2 Push-in connector 2-pole		
Cable	2 cables 0.3m with connector 2-pole		
Protection class IEC	Safety class III		
Initial Performance (IEC Compliant)			
Luminous flux tolerance	+/-10%		

Power consumption tolerance	+/-10%
Product Data	
Order product name	BVP375 1LED 30K 24V 35 10W COB
Full product name	BVP375 1LED 30K 24V 35 10W COB
Full product code	872110370224199
Order code	911401733784

Material Nr. (12NC)	911401733784
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103702241
Numerator - Packs per outer box	40
EAN/UPC - Case	8721103702241

Dimensional drawing

