



UniSpot

BVP375 1LED RGB 24V 10 DMX 10W

UniSpot, 240 lm, 10 W, Red, green and blue, DMX, Safety class III

Philips UniSpot features a sophisticated and compact design that balances beauty and functionality, unobtrusively blending into diverse urban applications. Spotlights in the UniSpot range feature a cylindrical geometry separated into two sections. The front section provides illumination, while the back section connects to heating or other systems using a variety of accessories. Two indication plates on the stand and base make the installation process simple and easy.

Product data

General Information		Protection class IEC	
Driver included	No	Safety class III	
Light Technical		Controls and Dimming	
Luminous Flux	240 lm	Dimmable	Yes
Correlated Color Temperature (Nom)	-	Control interface	DMX
Luminous Efficacy (rated) (Nom)	24 lm/W	Mechanical and Housing	
Color rendering index (CRI)	>80	Housing Material	Aluminum Alloy
Light source color	Red, green and blue	Optical cover material	Glass
Operating and Electrical		Housing Color	Dark gray
Input Voltage	24 V	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Line Frequency	- Hz	Mech. impact protection code	IK06 [1 J]
Power Consumption	10 W	Optical cover type	Clear glass
Power Factor (Fraction)	-	Net Weight (Piece)	0.500 kg
Connection	2 Push-in connector 5-pole	Approval and Application	
Cable	2 cables 0.3m with connector 5-pole	CE mark	Yes

Ambient temperature range	-40 to +50 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	BVP375 1LED RGB 24V 10 DMX 10W
Full product name	BVP375 1LED RGB 24V 10 DMX 10W

Full product code	872110370240199
Order code	911401733984
Material Nr. (12NC)	911401733984
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103702401
Numerator - Packs per outer box	40
EAN/UPC - Case	8721103702401

Dimensional drawing

